



15A, 125V HALF-CONTROLLED PLUG LOAD CONTROLLABLE RECEPTACLE, WHITE

5262CHW | Pass & Seymour

FEATURES & BENEFITS

Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with 2014 NEC®, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.





- Can be wired to any number of system-based or stand-alone plug load control solutions.
- Factory-broken split-circuit tab allows for 50% plug load control to be achieved in one duplex receptacle.
- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

SPECIFICATIONS

GENERAL INFO

Color: White Type: Receptacles

Duty: Hard Use Commercial Spec Grade

RoHS: Yes

CSA Listing Info: Yes CSA Listed: Yes

CSA Standard: File No. LR16063

Federal Spec: Yes UL Listing No: UL498

UL Standard: File No. E140596

UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.780" Height (US): 3.281" Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

Volts: 125V Volts (AC): 125 Capacity: Duplex

Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

