



## 15A, 125V HEAVY-DUTY SPEC GRADE PLUG LOAD TIMER RECEPTACLE, WHITE

PLT26251W | [Pass & Seymour](#)

### FEATURES & BENEFITS

New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of P&S Plug Load Controllable solutions will take a load off your mind and a load off your customers' electric bills.



- **Receptacle compliant with 2014 NEC, CA Title 24, and ASHRAE 90.1.**
- **Products meets requirements of UL498B:** Receptacles with integral switching means.
- **Power button on face** serves as a manual override to scheduled programs.
- **Two individual programs** can be set to automatically control plug loads.
- **Corrosion-resistant, plated steel strap** locked into face and back body to resist pulling away from face/body assembly.
- **Bottom half of device features a single receptacle** that is automatically controlled by the time clock.
- **Clear LCD display** shows program status, ON/OFF status, current time, and day of the week.
- **Feed-thru capability** allows for downstream control of multiple receptacles.
- **Center panel flips open** for easy, three button programming.
- **Permanently molded power symbol** on face identifies controlled receptacle in accordance with ASHRAE 90.1, NEC, and Title 24.
- **.032 inch thick, brass triple-wipe power contacts** for lasting retention.
- **Auto-ground** eliminates the necessity to terminate grounding conductor in device.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
CSA Listed: Yes  
CSA Standard: Yes  
cULus: Yes  
Federal Spec: Yes  
UL Listing No: UL498B  
UL Standard: 498B, 498, 244A

#### **CONSTRUCTION INFORMATION**

Material 1: Polycarbonate

#### **TECHNICAL INFORMATION**

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: Conforms to NEMA WD-1 and WD-6; Title 24 Compliant  
Volts: 125V  
Receptacle Type: Plug Load Timer  
Number Of Receptacles: Single