

PRODUCT SPECIFICATION

CATALOG NUMBER: See table below

DESCRIPTION: POLAR/SOLAR® extension cord with power indicator light in the

cord connector

APPROVALS: UL Listed and CSA Certified Outdoor Use Cord Set


CONSTRUCTION PARAMETERS:

Cable type: SEOOW, see table below for gauge

Cable jacket material: TPE, yellow

Cord rating: Extra Hard Usage per the National Electrical Code

Cable legend type: Indent print



Attachment plug configuration: NEMA 5-15P Cord connector configuration: NEMA 5-15R

Plug and connector material: Clear PVC, with neon power indicator lamp in the connector

ELECTRICAL AND ENVIRONMENTAL PROPERTIES:

Cable temperature rating: -50 to +105 °C
Nominal operating voltage: 125 VAC
Maximum operating current: See table below

Catalog no.	Gauge	Length	Current rating	Case qty	UPC
15670002	14/3	25 ft	15A	6	0 29892 01567 1
15680002		50 ft		4	0 29892 01568 8
15690002		100 ft	13A	3	0 29892 01569 5
17670002	12/3	25 ft	15A	6	0 29892 01767 5
17680002		50 ft		4	0 29892 01768 2
17690002		100 ft		3	0 29892 01769 9

This product complies with European Directive 2011/65/EU (RoHS-2,

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part.

We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is the proprietary intellectual property of Southwire Company LLC. Any information contained herein shall not be disclosed to any party without the written consent of Southwire Company LLC.