

## Single Phase Specifications

600 Primary Volts 120/240 Secondary Volts

60 Hz

kVA	Aluminum				Copper			
	Catalog Number	Approx. Weight (Lbs.)	Case Style	Mtg Type W - Wall F - Floor	Catalog Number	Approx. Weight (Lbs.)	Case Style	Mtg Type W - Wall F - Floor
15	XMF015PE	175	CH2	F/W	XMF015PEC	205	CH2	F/W
25	XMF025PE	260	CH3	F/W	XMF025PEC	275	CH3	F/W
37.5	XMF037PE	310	CH4	F/W	XMF037PEC	360	CH4	F/W
50	XMF050PE	350	CH4	F/W	XMF050PEC	395	CH4	F/W
75	XMF075PE	525	CH4	F/W	XMF075PEC	535	CH5	F
100	XMF100PE	578	CH7	F	XMF100PEC	609	CH6	F
150	XMF150PE	772	CH7	F	XMF150PEC	765	CH7	F
200	XMF200PE	964	CH7	F	XMF200PEC	1013	CH7	F

## Three Phase Specifications

600 Primary Volts 208Y/120 Secondary Volts

60 Hz

kVA	Aluminum		Copper		Case Style	Mtg Type W - Wall F - Floor
	Catalog Number	Approx. Weight (Lbs.)	Catalog Number	Approx. Weight (Lbs.)		
15	XMK015PB	160	XMK015PBCN	175	CH1	F/W
30	XMK030PB	250	XMK030PBCN	295	CH2	F/W
45	XMK045PB	310	XMK045PBCN	385	CH3	F/W
75	XMK075PB	465	XMK075PBC	530	CH4	F/W
112.5	XMK112PB	630	XMK112PBC	655	CH5	F
150	XMK150PB	805	XMK150PBC	855	CH6	F
225	XMK225PB	1150	XMK225PBC	1500	CH7	F
300	XMK300PB	1550	XMK300PBC	1800	CH8	F

480 Primary Volts 120/240 Secondary Volts

60 Hz

kVA	Aluminum				Copper			
	Catalog Number	Approx. Weight (Lbs.)	Case Style	Mtg Type W - Wall F - Floor	Catalog Number	Approx. Weight (Lbs.)	Case Style	Mtg Type W - Wall F - Floor
15	XMF015LE	180	CH2	F/W	XMF015LEC	205	CH2	F/W
25	XMF025LE	255	CH3	F/W	XMF025LEC	275	CH3	F/W
37.5	XMF037LE	315	CH4	F/W	XMF037LEC	360	CH4	F/W
50	XMF050LE	345	CH4	F/W	XMF050LEC	395	CH4	F/W
75	XMF075LE	480	CH4	F/W	XMF075LEC	540	CH5	F
100	XMF100LE	578	CH7	F	XMF100LEC	609	CH6	F
150	XMF150LE	772	CH7	F	XMF150LEC	765	CH7	F
200	XMF200LE	964	CH7	F	XMF200LEC	1013	CH7	F

480 Primary Volts 208Y/120 Secondary Volts

60 Hz

kVA	Aluminum		Copper		Case Style	Mtg Type W - Wall F - Floor
	Catalog Number	Approx. Weight (Lbs.)	Catalog Number	Approx. Weight (Lbs.)		
15	XMK015KB	160	XMK015KBCN	170	CH1	F/W
30	XMK030KB	250	XMK030KBCN	275	CH2	F/W
45	XMK045KB	310	XMK045KBCN	365	CH3	F/W
75	XMK075KB	465	XMK075KBC	525	CH4	F/W
112.5	XMK112KB	630	XMK112KBC	650	CH5	F
150	XMK150KB	805	XMK150KBC	850	CH6	F
225	XMK225KB	1150	XMK225KBC	1500	CH7	F
300	XMK300KB	1550	XMK300KBC	1800	CH8	F