

WLTDR-1W

1.2W LED Asymmetric Wall Light, Round Recessed Lighting

	Job Information		
	Project Name		Туре
	Location		
	Quantity		Date
	Contact/Phone		
	Notes		
1			

Features

Body Construction

The body is constructed from machined aluminum which acts as a heat sink for the 1.2W LED. Fixture can be rotated 360° to a fixed position for directional asymmetrical lighting. Provided with toolless push in connector allows for daisy chain option, to be used with 18-2 AWG LVT cable (not provided). Suitable for indoor use only, dry and damp locations.

Housing

The LED asymmetric wall light is installed in an aluminum housing which allow for enclosed wiring and the fixture to be installed where insulation is present. Housing includes a strain relief to secure electrical cables and two torsion clips for enhanced rigidity to recessed surface.

Power Consumption

This fixture operate on 24V constant voltage. Remote power supply required (See back for driver options).

Voltage Drop

Contact your Liteline representative for voltage drop calculation guidelines.

Light Output

This recessed light outputs a warm white (3000 K) colour temperature which provides 59 lumens.

Beam Spread

The fixture LED provides lighting with 45 degree beam spread.

Dimming

100%-5% dimming with compatible electronic and magnetic dimming

Installation

When installing WLFDR-1W in an insulated wall a vapour barrier (WL-VBE sold separately) and a pre-mounting plate (P-1750 sold separately) is required.

Applications


With the added directional control, this allows for multiple corridor/hallway sidewall recess lighting, in addition adding essential accent illumination for under cabinet, display and wall washing environments.

SPECIFICATION			
Approved Location	Damp		
Beam Angle	45°		
CCT	3000 K		
Certification	cETLus		
CRI	90+		
Cut-hole	1¾" (44mm)		
Dimming	Yes		
Insulation Contact	Yes		
Lumen	59		
Lumens per Watt	50		
Material	Aluminum		
Max. Temp.	40°C		
Min. Start Temp.	-20°C		
Power Supply Type	Constant Voltage		
Primary Voltage	24		
Projected Life	35,000 hrs		
Warranty	3 Years		
Watt	1.2W		



Description

This 1.2W asymmetric light provides quality illumination for ambient accent lighting in hallways, corridors, stairs and entrances. Powered by a 24V constant voltage power supply (sold separately). Fixture is IC rated, suitable for indoor use only.







Intertek

Notes: Accessories should be ordered separately. For additional options please consult your Liteline representative. Due to our continued efforts to improve our products, product specifications are subject to change without notice.

Ordering Guide



WLTDR-1W30K-90-ABK LED Tear Drop Round Wall Light,

LED Tear Drop Round Wall Light, Anodized Black, 1.2W, 45° beam spread, 3000 K, 90+ CRI.



WLTDR-1W30K-90-AL

LED Tear Drop Round Wall Light, Brushed Aluminum, 1.2W, 45° beam spread, 3000 K, 90+ CRI.



WLTDR-1W30K-90-FWH

LED Tear Drop Round Wall Light, Flat White, 1.2W, 45° beam spread, 3000 K, 90+ CRI.

Accessories



WL-VBE

LED Wall Light Vapour Barrier.



P-1750

1¾" LED Wall Light Pre-mounting Plate.

Liteline Corporation Copyright © 2018 All rights reserved. Telephone 416.996.1856 1.866.730.7704 Fax 905.709.5255 1.888.738.9736



Non Dimming Class II

Hardwire Drivers



LED-HWB-24V-24W

LED 24V, 24W Hardwire Box LED Driver with DC 2.1 jack.

LED-HWB-24V-36W

LED 24V, 36W Hard wire Box LED Driver with DC 2.1 jack.

LED-HWB-24V-60W

LED 24V, 60W Hard wire Box LED Driver with DC 2.1 jack.

Power feed required



LED-HWB-DC21-6-PF

DC 2.1 to bare leads power feed.

Maximum 10' to first fixture.

* Power feed required for all drivers with DC 2.1 iack.

Dimming Class II

Electronic Hardwire Drivers – DC 2.1 – Powered by Lutron®



LED-HWBDIM2-24-40

40W LED dimmable hardwire driver with DC 2.1 jack. 2-wire, 24V, powered by Lutron® Hi-lume® 1% 2-wire 120V LED driver.

LED-HWBDIM3-24-40

40W LED dimmable hardwire driver with DC 2.1 jack. 3-wire, 24V, powered by Lutron® Hi-lume® 1% Ecosystem/3-wire LED driver.

Electronic Hardwire Drivers - Hardwire



HWB-DIM-EDC-24V-25W

25W dimmable electronic hardwire driver, 24V.

HWB-DIM-EDC-24V-50W

50W dimmable electronic hardwire



HWB-DIM-EDC-24V-96W

96W dimmable electronic hardwire driver, 24V.

Power feed required



LED-HWB-DC21-6-PF

DC 2.1 to bare leads power feed.

Maximum 10' to first fixture.

* Power feed required for all drivers with DC 2.1 iack.

Magnetic Indoor/Outdoor Hardwire Drivers

driver, 24V.



HWB-DIM-MDC-24V-20W

20W LED magnetic dimmable hardwire driver. 24V.

HWB-DIM-MDC-24V-40W

40W LED magnetic dimmable hardwire driver, 24V.

HWB-DIM-MDC-24V-60W

60W LED magnetic dimmable hardwire driver, 24V.

HWB-DIM-MDC-24V-96W

96W LED magnetic dimmable hardwire driver, 24V.



HWB-DIM-MDC-24V-192W

192W LED magnetic dimmable hardwire driver, 24V.

Wiring Diagram

