

Quality AC Disconnects for the Electrical & HVAC Industry



A/C PULL-OUT DISCONNECT

- ⇒ Front Panel opens to side for easy access/wiring
- ⇒ UV protected Attractive design
- ⇒ Electrostatic paint for exceptional resistance to corrosion and fading
- ⇒ NEMA 3R - outdoor RAINPROOF WEATHERPROOF equipment
- ⇒ Removable door for fast installation
- ⇒ Padlock provision on cover to prevent unauthorized access
- ⇒ Increased wiring compartment capacity
- ⇒ Heavy duty steel construction
- ⇒ *Easy to remove* 1/2", 3/4", 1" concentric knockouts to meet any application
- ⇒ Line and load lugs easily accessible for ease of installation
- ⇒ All models 10,000 AIC rated
- ⇒ UL and cUL listed

MODEL #	TYPE	CABINET SIZE	AMP RATING	VOLTAGE	MAX HP RATING	PHASE	STANDARD PKG
ACD-1	Non-fused	6-3/4"H x 4-7/8"W x 2-1/8"D	60	120/240	10	1	6

WIRE RANGE DATA		
Connectors	Copper	
	Sol.	Str.
Line	14-10	14-2
Load	14-10	14-2
Equip. Grd.	12-10	12-4

LUG TIGHTENING TORQUE (lb-in)		
Screw Type	Wire Size	Torque
Slotted	14-10	32-35
	8	36-40
	6-4	41-35
	3-2	45-50

acdcol.new