


Catalogue Number	Alternate Cat. No.	Size or Description	Packaging		List Price
			Case	Box	
Jack Chain - Steel - Bright Zinc Plated					
JC10-50		T10 43lbs.	300	50	\$ 40.95 / c'
JC10-100		T10 43lbs.	600	100	\$ 40.95 / c'
JC10-250R		T10 43lbs.	250' <i>reel</i>		\$ 105.00/reel
JC10-250B		T10 43lbs.	250' <i>bucket</i>		\$ 105.00/bucket
JC12-50		T12 29lbs	300	50	\$ 38.43 / c'
JC12-300R		T12 29lbs	300' <i>reel</i>		\$ 116.00/reel
JC12-300B		T12 29lbs	300' <i>bucket</i>		\$ 116.00/bucket
JC14-100		T14 16lbs.	1000	100	\$ 36.00 / c'
LC2-100		#2 115lbs.	600	100	\$ 46.53 / c'
LC3-100		#3 90lbs.	600	100	\$ 32.84 / c'
LC3-300R		#3 90lbs.	300' <i>reel</i>		\$ 99.00/reel
LC3-300B		#3 90lbs.	300' <i>bucket</i>		\$ 99.00/bucket
LC4-100		#4 70lbs.	600	100	\$ 57.61 / c'
LC4-250B		#4 70lbs.	250' <i>bucket</i>		\$ 144.00/bucket
STAINLESS STEEL - #10 Jack Chain					
JC10-100-SS		#10 43lbs.		100	\$ 362.00 / c'



B = Bucket
R = Reel



*** Please note: 60 Buckets of Jack Chain on a skid. Custom labeling available on orders of 20 Buckets or More. ***

S-Hooks



S10		T10	1000	100	\$ 7.50
-----	--	-----	------	-----	---------

Poly Twine & Yellow Polypro Rope



	max pull strength		Reel Length		
PTW-1/4	1120 lbs.	1/4"	1,300'	\$	40.000
PTW-5/16	1450 lbs.	5/16"	975'	\$	40.000
PTW-3/8	2250 lbs.	3/8"	630'	\$	40.000
PTW-1/2	4200 lbs.	1/2"	335'	\$	40.000
PL-210	210 lbs	Poly-Tying Twine	6,500' / Pail	\$	38.000

Caution Tape



<i>Non-Detectable</i>					
1591	Yellow "CAUTION" 4 mil	3" X 300'	-	16	\$ 900.00
1592		3" X 1000'	-	8	\$ 2,550.00
1593	Red "CAUTION BURIED ELECTRIC LINE BELOW" 4 mil	3" X 200'	-	16	\$ 810.00
1594		3" X 1000'	-	8	\$ 2,550.00
1595		6" X 1000'	-	4	\$ 5,340.00
<i>Detectable</i>					
1596	Red "CAUTION BURIED ELECTRIC LINE BELOW" 5 mil	2" x 1000'	-	8	\$ 7,906.00
1597		3" X 1000'	-	8	\$ 8,556.00
1598		6" X 1000'	-	4	\$ 15,600.00