



**Manufacturer Suggested Trade Price
120 Volt Standard Mats**

Effective: October 1, 2008

Last Updated: May 1, 2010

Model #	Dimensions (inches)	Dimensions (feet)	Price	Amps
F1006	40"x27"	3'4" x 2'3"		0.8
F1008	40"x32"	3'4" x 2'8"		0.9
F1010	40"x40"	3'4" x 3'4"		1.1
F1012	40"x48"	3'4" x 4'		1.3
F1206	48"x24"	4' x 2'		0.8
F1208	48"x30"	4' x 2.5'		1.0
F1209	48"x36"	4' x 3'		1.2
F1212	48"x48"	4' x 4'		1.6
F1506	60"x24"	5' x 2'		1.0
F1508	60"x30"	5' x 2.5'		1.3
F1509	60"x36"	5' x 3'		1.5
F1510	60"x42"	5' x 3.5'		1.8
F1512	60"x48"	5' x 4'		2.0
F1515	60"x60"	5' x 5'		2.5
F1806	72"x24"	6' x 2'		1.2
F1808	72"x30"	6' x 2.5'		1.5
F1809	72"x36"	6' x 3'		1.8
F1810	72"x42"	6' x 3.5'		2.1
F1812	72"x48"	6' x 4'		2.4
F1815	72"x60"	6' x 5'		3.0
F1818	72"x72"	6' x 6'		3.6
F2106	84"x24"	7' x 2'		1.4
F2108	84"x30"	7' x 2.5'		1.8
F2109	84"x36"	7' x 3'		2.1
F2110	84"x42"	7' x 3.5'		2.5
F2112	84"x48"	7' x 4'		2.8
F2115	84"x60"	7' x 5'		3.5
F2118	84"x72"	7' x 6'		4.2
F2121	84"x84"	7' x 7'		4.9

Model #	Dimensions (inches)	Dimensions (feet)	Price	Amps
F2506	96"x24"	8' x 2'		1.6
F2508	96"x30"	8' x 2.5'		2.0
F2509	96"x36"	8' x 3'		2.4
F2510	96"x42"	8' x 3.5'		2.8
F2512	96"x48"	8' x 4'		3.2
F2515	96"x60"	8' x 5'		4.0
F2518	96"x72"	8' x 6'		4.8
F2521	96"x84"	8' x 7'		5.6
F2525	96"x96"	8' x 8'		6.4
F2706	108"x24"	9' x 2'		1.8
F2708	108"x30"	9' x 2.5'		2.3
F2709	108"x36"	9' x 3'		2.7
F2710	108"x42"	9' x 3.5'		3.2
F2712	108"x48"	9' x 4'		3.6
F2715	108"x60"	9' x 5'		4.5
F2718	108"x72"	9' x 6'		5.4
F2721	108"x84"	9' x 7'		6.3
F2725	108"x96"	9' x 8'		7.2
F2727	108"x108"	9' x 9'		8.1
F3006	118"x24"	10' x 2'		2.0
F3008	118"x30"	10' x 2.5'		2.5
F3009	118"x36"	10' x 3'		3.0
F3010	118"x42"	10' x 3.5'		3.4
F3012	118"x48"	10' x 4'		3.9
F3015	118"x60"	10' x 5'		4.9
F3018	118"x72"	10' x 6'		5.9
F3021	118"x84"	10' x 7'		6.9
F3025	118"x96"	10' x 8'		7.9
F3027	118"x108"	10' x 9'		8.9
F3030	118"x116"	10' x 10'		9.5

If standard mats don't meet your needs Nuheat can custom make a mat to fit any shape or size in just 3 days! For more information contact your Nuheat representative at 800-778-9276.

Controls

Model #	Description	Price
SOLO	Solo Programmable Dual Voltage Thermostat	
TEMPO	Tempo Non-programmable Dual Voltage Thermostat	
HMY110	Harmony Programmable Thermostat	
DIMMER	Dimmer Switch	

Miscellaneous Materials

Model #	Description	Price
AC0006	Relay 120V Input & Load Relay 20 Amps	
AC0012	Extra Lead Length (standard length 10')	
AC0014	Heating Wire Repair Kit	
AC0016	Lead Wire Repair Kit	
AC0008	Floor Sensing Probe	
AC0100	Electric Fault Indicator	