

SIEMENS LOW VOLTAGE LOAD CENTER CSA LISTED. 3-PHASE MAIN LUG AND MAIN BREAKER 24-CIRCUITS. MAIN CURRENT RATING 225A. SPECIAL FEATURES: WITHOUT DOOR, ALUMINUM BUS BAR, ENCLOSURE NEMA TYPE 1, GREY.

Configuration of the busbars	225A
Mounting type	Combination
Phase number	1
Suitability for operation	Residential

Electricity

Ampacity	225 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V

Model

Product brand name	Siemens
Product sub brand name	Load Centers

Mechanical Design

Depth [in]	38.3 in
Height [in]	12 in
Width [in]	42618 in

last modified: 09/16/2018