

SIEMENS LOW VOLTAGE LOAD CENTER CSA LISTED. 1-PHASE MAIN BREAKER 32-CIRCUITS. MAIN CURRENT RATING 200A. SPECIAL FEATURES: TOP MOUNTED, WITHOUT DOOR, ALUMINUM BUS BAR, ENCLOSURE NEMA TYPE 1, GREY.

Configuration of the busbars	200A
Mounting type	Surface
Phase number	1
Suitability for operation	Residential

Electricity

Ampacity	200 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V

Model

Product brand name	Siemens
Product sub brand name	Load Centers

Mechanical Design

Number of width units for installation width	32
Size of the circuit-breaker	MB
Width [in]	2711.64 in

last modified: 03/12/2018