




VAPOR BARRIER NON-METALLIC CABLE BOXES

4 in. Round Vapor Barrier Cable Box - For Ceiling
2-5/8 in. Deep, 27.1 Cu. in., 1/2 in. Setback

A83



Catalog #: 2027FBAR

APPLICATIONS

Vapor barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment from elements outside the structure
RACO® nonmetallic vapor barrier cable boxes provide the installer with a cost alternative that is lightweight and easy to install and provide excellent protection for wiring system or devices
RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires and accommodate wiring devices such as switches and receptacle

PRODUCT FEATURES

Self-clamping wire entry clamps
Vapor/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
Hands free installation for 1/2", 5/8", or 3/4" drywall
Front mounted grounding screw with combination straight/Robertson head
N/A

CSA

CSA C22.2 #18

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable
Color: Yellow

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No
Fixture (Static) Lbs.: 50

CONFIGURATION

Cable Clamps: 4
Bracket Type: Flush
Bracket Setback: 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-5/8 in.

PRODUCT MEASUREMENTS

Depth: 2-5/8 in.
Cubic Inches (cm3): 27.15 (444.8)
Wt. Ea. (Lbs.): 0.317
Product Length (in.): 7.00
Product Width (in.): 2.75
Product Height (in.): 5.25

PACKAGING

Minimum Pack Qty.: 40
Std. Pkg.: 40
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 31.65
Ship Carton Length (in.): 25.50
Ship Carton Width (in.): 11.38
Ship Carton Height (in.): 10.00
Ctn Weight (Lbs.): 12.66
Pallet Qty: 960
UPC Number: 805035051528
I2of5: 30805035051529