

S3L 160 1000V R 80 Im= 800 3p F F



S3L 160 1000V R 80 Im= 800 3p F F



General Information

Extended Product Type	S3L 160 1000V R 80 Im= 800 3p F F
Product ID	1SDA050438R1
EAN	8015644505929
Catalog Description	S3L 160 1000V R 80 Im= 800 3p F F
Long Description	CIRCUIT-BREAKER ISOMAX S3L 160 1000V THREE-POLE FIXED WITH FRONT TERMINALS AND PROTECTIVE RELEASES THERMOMAGNETIC IN AC R 80-800 A

Ordering

EAN	8015644505929
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	178 mm
Product Net Height	233 mm
Product Net Length	200 mm
Product Net Depth / Length	0.1035 m
Product Net Weight	2.6 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Height	233 mm
Package Level 1 Depth / Length	178 mm
Package Level 1 Gross Weight	5.6 kg
Package Level 1 EAN	8015644505929

Additional Information

Power Loss	30 W
Product Main Type	SACE Isomax
Product Name	Moulded Case Circuit Breaker
Sub-type	S3
Suitable For	Isomax S3

Suitable for Product Class

Isomax

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	ITSCE-604050012
Declaration of Conformity - CE	1SDL000286R001
Instructions and Manuals	ITSCE-601780022 ITSCE-605071013

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
Object Classification Code	Q

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Isomax

Low Voltage Products and Systems → Circuit Breakers → Service → Replacements

