

T4V 250 TMA 125-1250 3p F FC 1150V AC



Products → Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

General Information

Extended Product Type:	T4V 250 TMA 125-1250 3p F FC 1150V AC
Product ID:	1SDA063414R1
EAN:	8015644660338
Catalog Description:	T4V 250 TMA 125-1250 3p F FC 1150V AC
Long Description:	C.BREAKER TMAX T4V 250 1150V AC FIXED THREE-POLE WITH FRONT TERMINALS F OR CABLE Cu AND THERMOMAGNETIC RELEASE TMD R 125-1250 A

Ordering

EAN:	8015644660338
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85352100

Dimensions

Product Net Weight:	1 kg
----------------------------	------

Container Information

Package Level 1 Units:	1 piece
-------------------------------	---------

Additional Information

Number of Poles:	3
Power Loss:	at Rated Operating Conditions per Pole 6.2 W
Product Main Type:	SACE Tmax T
Product Name:	Moulded Case Circuit Breaker
Product Type:	CB
Rated Current (I_n):	Main Circuit 125 A
Rated Operational Voltage:	1150 V AC 1000 V DC
Rated Service Short-Circuit Breaking Capacity (I_{cs}):	(1000 V AC) 12 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}):	(415 V AC) 200 kA (1000 V AC) 20 kA
Rated Uninterrupted Current (I_u):	250 A
Release Type:	TM
Standards:	IEC
Sub-type:	T4
Terminal Connection Type:	Fixed Circuit-Breakers Front for Copper Cables
Version:	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SDC210015D0208
Declaration of Conformity - CE:	1SDL000165R0004
GL Certificate:	1SDL000163R0061
Instructions and Manuals:	1SDH000457R0001

Classifications

ETIM 4:	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5:	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6:	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
Object Classification Code:	Q