

### General Information

<b>Extended Product Type:</b>	RB121A110-220VAC/D
<b>Product ID:</b>	1SNA610132R2300
<b>EAN:</b>	3472596101329
<b>Catalog Description:</b>	RB121A-110-220VAC/DC R1800 screw relay 1 c/o, A1-A2=110/220VAC/DC, 380V/8A, LED
<b>Long Description:</b>	RB121A-110-220VAC/DC R1800 screw relay 1 c/o, A1-A2=110/220VAC/DC, 380V/8A, LED

### Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

### Ordering

<b>EAN:</b>	3472596101329
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85364900

### Dimensions

<b>Product Net Width:</b>	18 mm
<b>Product Net Height:</b>	65 mm
<b>Product Net Depth:</b>	62 mm
<b>Product Net Weight:</b>	0.047 kg

### Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	65 mm
<b>Package Level 1 Height:</b>	77 mm
<b>Package Level 1 Length:</b>	20 mm
<b>Package Level 1 Gross Weight:</b>	0.054 kg

### Environmental

<b>Ambient Air Temperature:</b>	Operation -20 ... 55 °C Storage -40 ... 80 °C
---------------------------------	--

### Classifications

<b>ETIM 4.0:</b>	EC001437 - Switching relay
<b>ETIM 5.0:</b>	EC001437 - Switching relay
<b>eClass:</b>	7.0 27371601

