



## MBCC-530

### ▶ SINGLE-ENDED CORDSETS



Mini-style Quick Disconnect Cable  
 5 Pin Female Pin-out Straight Connector  
 9 m (30 ft) in Length  
 Nylon coupling nut  
 Part Number: 29950

#### CERTIFICATIONS



#### SPECIFICATIONS

Number of Contacts	5
Number of Connectors	1
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector Body Material/Color	PUR Black
Outside Cable Diameter (mm)	7
Cordset Length (m)	9.14
Trunk Length (m)	No Trunk
Coupling Material/Color	Nylon Black

By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our [privacy policy](#).

<b>Maximum Temp. (°C)</b>	105
<b>Current Rating (A)</b>	9.0
<b>Minimum Temp. (°C)</b>	-40
<b>Voltage Rating (V)</b>	300 V ac/dc
<b>IP Rating</b>	IP67
<b>Primary Connector Type</b>	MINI
<b>Primary Coupling Method</b>	7/8"-16
<b>Primary Gender</b>	Female
<b>Primary Orientation</b>	Straight
<b>Primary Number of Conductors</b>	5
<b>Primary AWG</b>	18
<b>Secondary Connector Type</b>	Flying Leads
<b>Feature: Hazardous Area</b>	No
<b>Oil/Grease Resistant</b>	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America

By accepting cookies, we give you the best experience throughout our site, including access to My Account, My Library, and My Wish List. To learn more, visit our privacy policy.