

## MICRO SENSORS AND SWITCHES INLINE CHANNEL MOUNTED

### DESCRIPTION

Four unique sensors that can work inline, remote, and/or be built into the channel itself.

### FEATURES

- \* Micro push button on/off only
- \* Touch with dimming and memory
- \* Proximity (swipe hand near sensor) on/off only
- \* PIR timed 6-70s

\*CUSTOM PRE-INSTALLATION ASSEMBLY AVAILABLE UPON REQUEST\*

### SPECIFICATIONS

Input Voltage: 24VDC  
Loading Power: 8A Max

### MEASUREMENTS

CRTB01 -- 17.1mm x 80mm  
CRTT03 -- 17.1mm x 80mm  
CRTSPIRIT -- 17.1mm x 100mm  
CRTS01 -- 17.1mm x 85mm



### CRTB01 -- Micro Button Switch

One touch on/off switch



### CRTT03 -- Dimming Touch Switch

Blue light identifying where to touch to control  
Hold to dim on/off



### CRTSPIRIT -- PIR Motion Sensor

Adjustable timer controlling the length of time the lights stay on from 6 to 70 seconds



### CRTS01 -- Proximity Hand Sensor

On/off function only  
Swipe hand past sensor to activate

Project: \_\_\_\_\_

Type: \_\_\_\_\_

Date: \_\_\_\_\_

Part #: \_\_\_\_\_

## DESCRIPTION

Three unique sensors offering solutions to a wide range of applications.

## FEATURES

- \* Flush circular dimmable touch switch with memory (offered in black and white)
- \* Dimmable sub-surface switch capable of sensing touch through wood, composite, or glass surfaces up to 30mm thick
- \* Interchangeable door/hand operated multi-sensor switch

## SPECIFICATIONS

Input Voltage: 24VDC  
Loading Power: 8A Max



### CRTT04B / CRTT04W -- Dimming Touch Switch

Dimensions: 22mm diameter (Hole required is 18mm diameter)  
Flush circular dimmable touch switch  
Available in black and white

Pictures Coming  
Soon!

### CRTT006 -- Dimming Touch Surface Switch

Dimmable sub-surface switch capable of sensing touch through wood, composite, or glass surfaces up to 30mm thick



### CRTSIRDH -- Door / Hand Sensor

Detection Range:  $\leq 10$  cm

Project: \_\_\_\_\_

Type: \_\_\_\_\_

Date: \_\_\_\_\_

Part #: \_\_\_\_\_