
Cabinet19x28x24_1305030760_Eng



NO.	DESCRIPTION			
1	FRAME 22 x 31 x 18			
2	rear section (19 x 28)	1		
3	PLEXI. DOOR (19 X 28)	1		
4	REAR MALE HINGE	2		
5	FRONT FEMALE HINGE	2		
6	MOUNTING RAIL (1.25") TAPPED 10-32	2		
7	4" FAN CUTOUT COVER PLATE	2		
8	LINK ROTARY LATCH, MEDIUM	2		
9	KEEPER	2		
10	THREAD ROLLING PAN HEAD - PHILLIPS	10		
11	CLEVIS PIN 3/8 x 3/4	2		
12	HAIRPIN COTTER PIN 1-1/4"	2		

NOTES:

1 - CAPACITY: 150 LB

2 - WEIGHT: 106 LB

3 - CABINET IS FULLY REVERSIBLE LH OR RH SWING.



PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF

DRAWING IS THE SOLE PROPERTY OF
A.I.G. ELECTRON METAL INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
A.I.G. ELECTRON METAL INC IS PROHIBITED.

	DRAWN BY:
1	TOM
	CHECKED BY:

Title:

WALL MOUNT CABINET 16RU (19 x 28) x 24

PROJECT:	FILE:				
WallMount\Cabinet2013\Ensemble	Cabinet19x28x24_1305030760_Eng				
PART NO.: WMCRE1-191624	1305030760	B	1:12	2011-10-26	1 / 2

4

A.I.G. ELECTRON METAL INC IS PROHIBITED.

3

PROJECT: WallMount\Cabinet2013\Ensemble	Cabinet19x28x24_1305030760_Eng				
WMCRE1-191624	1305030760	B B	1:16	2011-10-26	2 / 2

5