

FEM12

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	FEM12
Product ID:	1SNA118618R0100
EAN:	3472591186185
Catalog Description:	FEM12 End Sections Grey
Long Description:	FEM12 - End Sections - Grey - 3mm Spacing



Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Sections

Ordering

EAN:	3472591186185
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	3.20 g
----------------------------	--------

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Gross Weight:	0.06400 kg
Package Level 1 EAN:	3472591186185
Package Level 2 Units:	1000 piece
Package Level 3 Units:	48000 piece

Environmental

Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
---------------------------------	--

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Additional Information

Ambient Temperature:	-5 +40 °C
Color:	Grey
Function:	End Sections
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	FEM12
Product Name:	End Section
Spacing:	3 mm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1009
GOST Certificate:	1SND161005A1104
RoHS Information:	1SND230478F0202

Classifications

E-nummer:	2925606
ETIM 4.0:	EC000886 - Endplate and partition plate for terminal block
ETIM 5.0:	EC000886 - Endplate and partition plate for terminal block
Object Classification Code:	X
