

Powertech Controls Co., Inc.

909 Motor Parkway,

Hauppauge, NY 11788 US

Phone: 800.938.6678 • **Fax:** 888.368.8943**E-Mail:** info@powertechcontrols.com • **Web site:** <http://www.powertechcontrols.com>

[All Categories](#) > [Manufacturers](#) > [General Electric](#) > [General Electric \(GE\) Pilot and Signaling Devices](#) > [30 MM Devices](#) > [Heavy-Duty 30.5 mm Watertight/Oiltight Push Buttons](#) > [Standard Indicating Lights](#) > [Item # CR104PLG88L](#)

[larger image](#)**Item # CR104PLG88L, Standard Indicating Lights****Unit Price \$70.20**

Suitable for use in NEMA Types 1, 3, 3R, 4, 4X, 12, and 13 applications when mounted in enclosures rates for those same applications. For some NEMA Type 4X applications, protective caps will improve cor

Specifications

Power Supply Type	Full Voltage
Supply Voltage	24 VAC/DC
Lamp Type	LED, 24V
Color	Blue
Rated Current	10 Amperes Continuous A
Rated Voltage	600 Volts Maximum AC/DC V
Item Details	Not suitable for use with NEON light.

[Print](#)[Back](#)