Page 1 of 2

2" Wide 1 3/8" Deep, 22", 34", 46" or 92" Lengths, 1 or 2 Lamp, T5

Features

- Only 2" wide.
- Utilizes compact, high efficency, T5 or T5HO lamps.
- · Fully enclosed wiring.
- Optional white or specular, symmetric and assymetric reflector.
- Convenience outlet and switch K.O.s provided
- Push through lamp holders with rotor for secure lamp retention.
- Optional hangers and wires guards.








Dimensions


A: 9/16"(14mm) K.O. B: 7/8"(22mm) K.O.


C: CARRIAGE SLOT














Job Information	Туре:	
Job Name:		
Cat. No.:		
Lamp(s):		
Volts/Ballast:		

Lightolier a Genlyte Thomas Company www.lightolier.com Technical Information: (978) 657-7600 • Fax (978) 658-0595 631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710 We reserve the right to change details of design, materials and finish. Copyright 2002 Lightolier Section 3A/Folio H120-17






Narrow T5 Strip **SV T5 Strip**


Page 2 of 2

2" Wide 1 3/8" Deep, 22", 34", 46" or 92" Lengths, 1 or 2 Lamp, T5

Photometry





Model No. SV4S228120PG



Ordering Information

Explanation of Catalog Number. Example: SV4S228120PG





10 THD (54 watt only)

Options & Accessories

Stem and Canopy Sets: Suspend luminaire 12", 18", 24", 36", or 48" from surface. (Two per luminaire is recommended. For 34" and 46"SV Strip only.) Catalog number: SV5F12 (12"); SV5F18 (18"); SV5F24 (24"); SV5F36 (36"); SV5F48 (48").

Chain Hanging Kit: Includes two 5' heavy duty link chains with sturdy "V" hook for fixture suspension. (34" and 46" Strip only.) Catalog number: EE9HC Wire Guard: White wire guard. Catalog number: For SV Strip T5 34"; SV5GXW3. For SV Strip T5 46"; SV5GXW4.

Reflector: Consult specification sheet (folio H120-22 & H120-20). Radio Interference Filter: 120, 277 or UNV volt, 50 or 60 Hz. Suffix: R Ballast Options: For other ballast options, consult factory

Specifications

Materials: Chassis parts are die-formed heavy gauge cold rolled steel,1-3/8" deep x 2" channel width.

Specifications (continued)

Finish: Chassis exterior - phosphate undercoating, baked white acrylic matte high reflectance paint finish.

Electrical: HPF, thermally protected class "P" ballast. If K.O.s are within 3" of ballast use wire suitable for at least 90°.

Labels: Listed by



Job Information

Type:

www.lightolier.com **Lightolier** a Genlyte Thomas Company Technical Information: (978) 657-7600 • Fax (978) 658-0595 631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710 We reserve the right to change details of design, materials and finish. Section 3A/Folio H120-17 Copyright 2002 Lightolier

