

BJM10

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	BJM10
Product ID:	1SNA173615R2500
EAN:	3472591736151
Catalog Description:	BJM 10 10 POLES Jumper Bars
Long Description:	BJM10 - Jumper Bars - 10 poles - - 10mm Spacing



Categories

Products » Low Voltage Products and Systems » Connection Devices »
 Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591736151
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	27.00 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.27000 kg
Package Level 1 EAN:	3472591736151
Package Level 2 Units:	400 piece
Package Level 2 Width:	175 mm
Package Level 2 Height:	260 mm
Package Level 2 Length:	227 mm
Package Level 3 Units:	19200 piece

Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BJM
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 57 A
Sub-Function:	Assembled jumper bar
Sub-Function 2:	Screw

Certificates and Declarations (Document Number)

GOST Certificate:	1SND161005A1104
--------------------------	-----------------

RoHS Information: 1SND230492F0201

Classifications

E-nummer: 2925706
ETIM 4.0: EC000489 - Cross-connector for terminal block
ETIM 5.0: EC000489 - Cross-connector for terminal block
Object Classification Code: X
