

M6/8.P

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	M6/8.P
Product ID:	1SNA165114R1700
EAN:	3472591651140
Catalog Description:	M6/8.P Screw Clamp Terminal Blocks - Ground - Green-Yellow
Long Description:	M6/8.P Screw Clamp Terminal Blocks - Ground - Green-Yellow,6mm ² RatedCrossSection, 8mm Spacing G32, TH 35-7.5, TH 35-15 Rail



Categories

Products » Low Voltage Products and Systems » Connection Devices »
Terminal Blocks » Screw Clamp Terminal Blocks

Ordering

EAN:	3472591651140
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	8.0 mm
Product Net Height:	43.5 mm
Product Net Depth:	40.5 mm
Product Net Weight:	26.00 g

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	81 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	1.30000 kg
Package Level 1 EAN:	3472591651140
Package Level 2 Units:	750 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	19.850 kg
Package Level 3 Units:	36000 piece
Product Packing Type:	Box

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Technical UL/CSA

Connecting Capacity-Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22-8 AWG
---	---------------------------------

Connecting Capacity UL/CSA: Screw Clamp / Rigid 22-8 AWG
Flammability According to UL94: V0

Additional Information

Color: Green-Yellow
Connecting Capacity-Main Circuit: Screw Clamp / Flexible 1x 0.5-6 mm²
Screw Clamp / Rigid 1x 0.5-10 mm²
Connection Type: Screw clamp
Function: Ground
Gauge Type: A5
IIT Publishing Status: Level 0 - Information enabled
Mounting on DIN Rail: G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715
TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels: 1
Product Main Type: M6/8.P
Product Name: Terminal block
Rated Cross-Section: 6 mm²
Rated Short-time Withstand Current (I_{cw}): for 1.0s 720 A
Recommended Screw Driver: 4.5 mm
RoHS Date: 20050818
Spacing: 8 mm
Sub-Function: 2 connections
Sub-Function 2: Screw rail connection
Wire Stripping Length: 12.0 mm

Certificates and Declarations (Document Number)

BV Certificate: 1SND163013A0200
CSA Certificate: 1SND161039A0201
cUL Certificate: 1SND161011A0202
Declaration of Conformity - CE: 1SND225004C1008
GOST Certificate: 1SND161005A1104
RoHS Information: 1SND230023F0206

Classifications

E-nummer: 2925526
ETIM 4.0: EC000901 - Ground terminal block
ETIM 5.0: EC000901 - Ground terminal block
Object Classification Code: X
