



INFINITY OUTRIGGER®

ALL-WEATHER LOUDSPEAKERS

Don't let a little rain or salt spray come between you and your favorite music. Infinity Outrigger® indoor/outdoor loudspeakers feature waterproof drivers, rugged polypropylene enclosures and noncorrosive fasteners, so they're ideal for use around the pool or on the boat. But these speakers aren't just tough — they deliver sound quality that's tough to match. With powerful, responsive woofers for rich, detailed lows, and dome tweeters for clear, distinct highs, Outriggers are engineered to perform like the Infinity systems they are.

HIGHLIGHTS:

- **ACCURATE**—Two-way design for acclaimed Infinity sound
- **WEATHERPROOF**—Polypropylene enclosures with waterproof drivers
- **RUGGED**—Aluminum, brass and stainless-steel parts
- **VERSATILE**—May be mounted or placed vertically or horizontally

KEY SPECIFICATIONS:

- Smooth 133mm (4") low-frequency driver
- Fast 25mm (1") dome tweeter
- 60Hz–20kHz frequency range
- 80-watt power rating
- Wall-mounting hardware included

PRODUCT SPECIFICATIONS:

Frequency Range (± 3dB):	60Hz – 20kHz
Recommended Amplifier Power Range:	10 – 80 watts
Sensitivity (2.83V @ 1 meter):	86dB
Nominal Impedance:	8 ohms
Low-Frequency Driver:	133mm (5-1/4")
High-Frequency Driver:	25mm (1") dome tweeter
Operating Specifications:	–20°C to 60°C (– 4°F to 140°F) at any humidity level
Dimensions:	254mm x 203mm x 178mm (10" x 8" x 7")
Weight:	3.7kg (8.2 lb)