



**Manufacturer Suggested Trade Price**  
120 Volt Standard Mats

Effective: June 13, 2011

Last Updated: June 8, 2011

Model #	Dimensions (inches)	Dimensions (feet)	Price	Amps
F1006	40"x27"	3'4" x 2'3"	\$214.00	0.8
F1008	40"x32"	3'4" x 2'8"	\$223.00	0.9
F1010	40"x40"	3'4" x 3'4"	\$236.00	1.1
F1012	40"x48"	3'4" x 4'	\$254.00	1.3
F1206	48"x24"	4' x 2'	\$217.00	0.8
F1208	48"x30"	4' x 2.5'	\$232.00	1.0
F1209	48"x36"	4' x 3'	\$243.00	1.2
F1212	48"x48"	4' x 4'	\$290.00	1.6
F1506	60"x24"	5' x 2'	\$232.00	1.0
F1508	60"x30"	5' x 2.5'	\$249.00	1.3
F1509	60"x36"	5' x 3'	\$276.00	1.5
F1510	60"x42"	5' x 3.5'	\$298.00	1.8
F1512	60"x48"	5' x 4'	\$329.00	2.0
F1515	60"x60"	5' x 5'	\$381.00	2.5
F1806	72"x24"	6' x 2'	\$243.00	1.2
F1808	72"x30"	6' x 2.5'	\$276.00	1.5
F1809	72"x36"	6' x 3'	\$309.00	1.8
F1810	72"x42"	6' x 3.5'	\$344.00	2.1
F1812	72"x48"	6' x 4'	\$371.00	2.4
F1815	72"x60"	6' x 5'	\$423.00	3.0
F1818	72"x72"	6' x 6'	\$453.00	3.6
F2106	84"x24"	7' x 2'	\$258.00	1.4
F2108	84"x30"	7' x 2.5'	\$302.00	1.8
F2109	84"x36"	7' x 3'	\$344.00	2.1
F2110	84"x42"	7' x 3.5'	\$375.00	2.5
F2112	84"x48"	7' x 4'	\$408.00	2.8
F2115	84"x60"	7' x 5'	\$445.00	3.5
F2118	84"x72"	7' x 6'	\$511.00	4.2
F2121	84"x84"	7' x 7'	\$571.00	4.9

Model #	Dimensions (inches)	Dimensions (feet)	Price	Amps
F2506	96"x24"	8' x 2'	\$293.00	1.6
F2508	96"x30"	8' x 2.5'	\$329.00	2.0
F2509	96"x36"	8' x 3'	\$371.00	2.4
F2510	96"x42"	8' x 3.5'	\$408.00	2.8
F2512	96"x48"	8' x 4'	\$425.00	3.2
F2515	96"x60"	8' x 5'	\$487.00	4.0
F2518	96"x72"	8' x 6'	\$560.00	4.8
F2521	96"x84"	8' x 7'	\$648.00	5.6
F2525	96"x96"	8' x 8'	\$695.00	6.4
F2706	108"x24"	9' x 2'	\$309.00	1.8
F2708	108"x30"	9' x 2.5'	\$351.00	2.3
F2709	108"x36"	9' x 3'	\$395.00	2.7
F2710	108"x42"	9' x 3.5'	\$423.00	3.2
F2712	108"x48"	9' x 4'	\$453.00	3.6
F2715	108"x60"	9' x 5'	\$541.00	4.5
F2718	108"x72"	9' x 6'	\$626.00	5.4
F2721	108"x84"	9' x 7'	\$686.00	6.3
F2725	108"x96"	9' x 8'	\$743.00	7.2
F2727	108"x108"	9' x 9'	\$814.00	8.1
F3006	118"x24"	10' x 2'	\$324.00	2.0
F3008	118"x30"	10' x 2.5'	\$375.00	2.5
F3009	118"x36"	10' x 3'	\$417.00	3.0
F3010	118"x42"	10' x 3.5'	\$439.00	3.4
F3012	118"x48"	10' x 4'	\$485.00	3.9
F3015	118"x60"	10' x 5'	\$571.00	4.9
F3018	118"x72"	10' x 6'	\$670.00	5.9
F3021	118"x84"	10' x 7'	\$726.00	6.9
F3025	118"x96"	10' x 8'	\$800.00	7.9
F3027	118"x108"	10' x 9'	\$882.00	8.9
F3030	118"x116"	10' x 10'	\$944.00	9.5

**Shower Mat**

Model #	Description	Price	Amps
F032032-S	Shower Mat - 120V (32"x32" with 22' cold leads)	\$199.00	0.7

**Controls**

Model #	Description	Price	
SOLO	Solo Programmable Dual Voltage Thermostat	\$175.00	
TEMPO	Tempo Non-programmable Dual Voltage Thermostat	\$110.00	
HDV	Harmony Dual-Voltage Programmable Thermostat	\$175.00	*NEW*
DIMMER	Dimmer Switch	\$27.00	

**Miscellaneous Materials**

Model #	Description	Price
AC0006	Relay 120V Input & Load Relay 20 Amps	\$60.00
AC0012	Extra Lead Length (standard length 10')	\$8.00/ft
AC0014	Heating Wire Repair Kit	\$25.00
AC0016	Lead Wire Repair Kit	\$80.00
AC0008	Floor Sensing Probe	\$24.00
AC0100	Electric Fault Indicator	\$20.00



**Manufacturer Suggested Trade Price**  
240 Volt Standard Mats

Effective: June 13, 2011

Last Updated: June 8, 2011

Model #	Dimensions (inches)	Dimensions (feet)	Price	Amps
G1509	60"X36"	5' x 3'	\$276.00	0.8
G1510	60"X42"	5' x 3.5'	\$298.00	0.9
G1512	60"X48"	5' x 4'	\$329.00	1.0
G1515	60"X60"	5' x 5'	\$381.00	1.3
G1808	72"X30"	6' x 2.5'	\$276.00	0.8
G1809	72"X36"	6' x 3'	\$309.00	0.9
G1810	72"X42"	6' x 3.5'	\$344.00	1.1
G1812	72"X48"	6' x 4'	\$371.00	1.2
G1815	72"X60"	6' x 5'	\$423.00	1.5
G1818	72"X72"	6' x 6'	\$453.00	1.8
G2106	84"X24"	7' x 2'	\$258.00	0.7
G2108	84"X30"	7' x 2.5'	\$302.00	0.9
G2109	84"X36"	7' x 3'	\$344.00	1.1
G2110	84"X42"	7' x 3.5'	\$375.00	1.2
G2112	84"X48"	7' x 4'	\$408.00	1.4
G2115	84"X60"	7' x 5'	\$445.00	1.8
G2118	84"X72"	7' x 6'	\$511.00	2.1
G2121	84"X84"	7' x 7'	\$571.00	2.5
G2506	96"X24"	8' x 2'	\$293.00	0.8
G2508	96"X30"	8' x 2.5'	\$329.00	1.0
G2509	96"X36"	8' x 3'	\$371.00	1.2
G2510	96"X42"	8' x 3.5'	\$408.00	1.4
G2512	96"X48"	8' x 4'	\$425.00	1.6
G2515	96"X60"	8' x 5'	\$487.00	2.0
G2518	96"X72"	8' x 6'	\$560.00	2.4
G2521	96"X84"	8' x 7'	\$648.00	2.8
G2525	96"X96"	8' x 8'	\$695.00	3.2

Model #	Dimensions (inches)	Dimensions (feet)	Price	Amps
G2706	108"X24"	9' x 2'	\$309.00	0.9
G2708	108"X30"	9' x 2.5'	\$351.00	1.1
G2709	108"X36"	9' x 3'	\$395.00	1.4
G2710	108"X42"	9' x 3.5'	\$423.00	1.6
G2712	108"X48"	9' x 4'	\$453.00	1.8
G2715	108"X60"	9' x 5'	\$541.00	2.3
G2718	108"X72"	9' x 6'	\$626.00	2.7
G2721	108"X84"	9' x 7'	\$686.00	3.2
G2725	108"X96"	9' x 8'	\$743.00	3.6
G2727	108"X108"	9' x 9'	\$814.00	4.1
G3006	118"X24"	10' x 2'	\$324.00	1.0
G3008	118"X30"	10' x 2.5'	\$375.00	1.2
G3009	118"X36"	10' x 3'	\$417.00	1.5
G3010	118"X42"	10' x 3.5'	\$439.00	1.7
G3012	118"X48"	10' x 4'	\$485.00	2.0
G3015	118"X60"	10' x 5'	\$571.00	2.5
G3018	118"X72"	10' x 6'	\$670.00	3.0
G3021	118"X84"	10' x 7'	\$726.00	3.4
G3025	118"X96"	10' x 8'	\$800.00	3.9
G3027	118"X108"	10' x 9'	\$882.00	4.4
G3030	118"X116"	10' x 10'	\$944.00	4.8
G144036	144" x 36"	12' x 3'	\$523.00	1.8
G144060	144" x 60"	12' x 5'	\$782.00	3.0
G144072	144" x 72"	12' x 6'	\$946.00	3.6
G144096	144" x 96"	12' x 8'	\$1,195.00	4.8
G144108	144" x 108"	12' x 9'	\$1,325.00	5.4
G144120	144" x 120"	12' x 10'	\$1,459.00	6.0
G144140	144" x 140"	12' x 12'	\$1,638.00	7.0
G168096	168" x 96"	14' x 8'	\$1,419.00	5.6
G168108	168" x 108"	14' x 9'	\$1,549.00	6.3
G168120	168" x 120"	14' x 10'	\$1,638.00	7.0
G168140	168" x 140"	14' x 12'	\$1,837.00	8.2
G240120	240" x 120"	20' x 10'	\$2,160.00	10.0

**Controls**

Model #	Description	Price
SOLO	Solo Programmable Dual Voltage Thermostat	\$175.00
TEMPO	Tempo Non-programmable Dual Voltage Thermostat	\$110.00
HDV	Harmony Dual-Voltage Programmable Thermostat	\$175.00

\*NEW\*

**Miscellaneous Materials**

Model #	Description	Price
AC0007	Relay 240V Input & Load Relay 20 Amps	\$60.00
AC0013	Extra Lead Length (standard length 10')	\$8.00/ft
AC0014	Heating Wire Repair Kit	\$25.00
AC0017	Lead Wire Repair Kit	\$80.00
AC0008	Floor Sensing Probe	\$24.00
AC0100	Electric Fault Indicator	\$20.00