

FLIR MPX MULTI-FORMAT ME373A 4K Ultra HD WDR Fixed Audio Dome

ME373A 4K Ultra HD WDR Fixed Audio Dome The FLIR 4K Ultra HD WDR Fixed Audio Dome Camera offers exceptional performance with 8MP resolution, providing brilliant image clarity and an incredible level of detail in recordings. This camera is compatible with popular analog HD systems¹ and features a built-in microphone for audio monitoring.²

4K HD PICTURE QUALITY

4K Ultra HD (8MP 3840x2160) resolution provides the highest standard in image clarity and detail for evidence collection

- 4K (8MP) Ultra HD, 8MP@15fps, 5MP@20fps, 4MP@30fps, 2MP@30fps
- 1/2" CMOS, 3.6mm lens, 100ft/31m IR
- True WDR (up to 100dB) for improved detail in challenging lighting conditions

MULTI-FORMAT

Compatible with popular analog HD formats¹

- Upgrade to Ultra HD without the expense of re-cabling³
- Compatible with popular analog HD formats (up to 5 MP)¹ & backwards compatible with Analog DVRs
- Quick video output format adjustment directly from the camera

BUILT TO PERFORM

- Installation in challenging outdoor conditions
- IP67 weatherproof
- -22°F / -30°C Cold Climate Capable
- Long cable runs in 4K up to 700ft/214m ³

Specifications


Camera	ME373A
Imaging Device	Ultra HD 4K (8MP), 1/2" CMOS
Effective Pixels	3840(H) × 2160(V)
Imager Type	CMOS
Image Readout	Progressive Scan
Day / Night	Auto (ICR) / Color / B/W
Mechanical IR Cut Filter	Yes
IVIIn. IIIumination	0.1 Lux @F1.6 (Color) 0.01 Lux @ F1.6 (B/W)
S/N Ratio	≥65dB
Horizontal Field of View	87° (H) field of view
IR Illumination Distance	100ft/31m
IR Wavelength	850nm
IR On / Off Control	No
Video Output	BNC (4K MPX/CVI, 5/4MP/1080p / CVBS Multi-format) ¹
Electronic Shutter Range	1/3(1/4)~1/100,000
Optical	1/3(1/4)~1/100,000
Lens Type	Fixed
Mount Type	Board Type
Iris Type	Fixed Iris
Iris Control Type	AIS
Focal Length	3.6mm
Aperture	F1.6
Optical Zoom	N/A
Focus	Fixed
Video	
Frame rates (Maximum)	4K(8MP)@15fps (MPX/CVI), 5MP@20fps (AHD/TVI), 4MP@30fps (MPX/
	CVI), 1080p@30fps (MPX/CVI/AHD/TVI), 960H @30fps (CVBS)
Aspect Ratio	16:9
Wide Dynmic Range	True WDR
Dynamic Range	Up to 100dB
Backlight Compensation	BLC/HLC
White Balance	Auto / Manual
Gain Control	Auto / Manual
Noise Reduction	2D/3D DNR
Smart IR	Yes, Adjustable
Digital Zoom	4x
Video Mirroring/Rotation	Horizontal Mirror / Vertical Flip
Video Overlay	Time / Date / Camera / Custom
Window Blanking (Privacy)	Yes, up to 8 areas
Defog	No
Menu Languages	English / Spanish / Portuguese / Korean / Japanese / Chinese / Russian /
Mashaniat	Polish / French / German / Italian
Mechanical	Alternative Alterna
Material	Aluminum Alloy
Product Dimensions (Dia × H)	3.9 × 2.5" / 99 × 64mm
Product Weight	0.77lb / 0.35kg
Electrical	Vec full time
Analog Video Out (service only)	Yes, full time
Power Input	12V DC
Power Consumption (maximum)	7.1W
Current Consumption (maximum)	585mA
Additional Features	
Built-in Heater	No
Audio I/O	1 Input + Microphone built-in ²
Audio Encoding	G.711a / G.711u / PCM
Alarm I/O	No
Environmental	
Storage Temperature	-22°F ~ +140°F/-30°C ~ +60°C
Storage Humidity	Less than 90% RH
Operating Temperature	- 22°F ~ +140°F / -30°C ~ +60°C
Operating Humidity	Less than 90% RH
Cold Start Temperature	-22°F/-30°C
Ingress Protection	IP67 Rated
Vandal Resistance	N/A
Certifications	
Certifications	CE / FCC / RoHS

Disclaimers:


1. For analog HD format compatibility, please see the 'Frame Rates' information in the table above. 2. Audio is disabled by default. Audio recording and / or use of listen-in audio without consent is illegal in

2. Audio is disabled by default. Audio recording and 7 or use of listen-in audio without consent is liegal in certain jurisdictions. FLIR Systems, Inc. assumes no liability for use of its products that does not conform with local laws.
2. This assumes the state of the second state (individually second state) and state size and the second state of the second state.

3. This camera should only be used with a power adapter (individually grounded) and extension cable meeting the specifications listed in the Quick Setup Guide / Installation Guide. Failing to use cables or power adapters meeting the required specifications will adversely affect performance.



Dimensions



Ordering Information

ME373A: 8-41430-01942-8

Package Dimensions

ME373A: 6.1" \times 6.1" \times 5.3" / 155mm \times 155mm \times 135mm Weight: 1.4lbs / 0.6kg

For latest accessory / mount compatibility visit http://flir.com/security/cameramounts

MARKHAM, ONTARIO

FLIR Systems, Inc. 250 Royal Crest Court Markham, ON L3R 3S1 Canada PH: +1 866.344.4674

PORTLAND

Corporate Headquarters FLIR Systems, Inc. 27700 SW Parkway Ave. Wilsonville, OR 97070 USA PH: +1 866.477.3687

www.flir.com/security NASDAQ: FLIR

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. @2018 FLIR Systems, Inc. All rights reserved. (Created 01/25/18) - (18-0159-SEC)

