

14W Med EL/SWP 1LP

Product family description

Philips Compact Fluorescent Energy Savign Soft White Plus lamps provide energy svings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

Features/Benefits

- Direct replacement for incandescent bulbs
- Provides warm and inviting soft white light
- Fits into incandescent fixtures
- Shape and size similar to an incandescent A19
- Long Life
- Lasts at least 7 years*
- Energy Savings
- Saves up to \$44 over the life off the lamp when you replace a 75W A19 incandescent lamp with a 20W Energy Saver Soft White Plus Lamp.**

Applications

• Ideal for Table/Floor Lamps, Outdoor Postlights, Wall Sconces, Reading Lamps, Border Lights, Open Hanging Fixtures and Ceiling Fans.

Notes

- Based on an average daily usage of 3-4 hours per day, 7 days per week.
- **Energy savings based on wattage saved x replacement lamp rated average life (8000 hours) = 1000 x \$.10 kWh rate.
- Approximate initial lumens the lamp lumen output is based upon lamp perfromance after 100 hours of operating life under standard laboratory conditions.
- Rated Average Life Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours.
- Energy savings over rted average life compared to incandescent equivalent based on \$.10 kWh rate. Use in recessed cans or enclosed fixtures could result in reduced life.
- Amalgam technology provides stable light output from -10F to 140F.

Product data		
Product Number	157008	
Full product name	14W Med EL/SWP 1LP	
Ordering Code	EL/A SWP 14W	
Pack type	1 Lamp	
Pieces per Sku	1	



Product data		
Skus/Case	6	
Pack UPC	046677157005	
EAN2US		
Case Bar Code	50046677157000	
Successor Product number		
Base	Medium [Single Contact Medium Screw]	
Bulb	EL/SWP	
Packing Type	1LP [1 Lamp]	
Packing Configuration	6	
Rated Avg. Life [3 hr Start]	8000 hr	
Ordering Code	EL/A SWP 14W	
Pack UPC	046677157005	
Case Bar Code	50046677157000	
Energy Saving	Energy Saving	
Watts	14W	
Color Rendering Index	82 Ra8	
Color Temperature	2700 K	
Initial Lumens	800 Lm	
Max Overall Length (MOL) - C	4.4 in	
Product Number	157008	




CI-SWP



Base Medium





Energy Saving Product

Energy Saving Energy Saving

CI-SWP

