


24VDC LEDTask™ Dry Location GMEXT LED Tape



PRODUCT DESCRIPTION

GM Lighting's 24VDC GMEXT Series enables extremely long runs from a single lead in a dry or wet location flexible LED tape. Available in 2700K, 3000K, 3500K and 4000K. Field cuttable and connectable for dry location only.

Factory cut only - cutting in field will void ETL label and warranty.

PROJECT TYPE

CATALOG NUMBER (FOR CUSTOM LENGTHS, PLEASE SEE ORDERING EXAMPLE BELOW)

KEY FEATURES

- 24VDC
- Mounts with 3M VHB[™] double stick tape
- Sure-Tite flexible tape to tape and tape to power supply connectors available (see below).
- Dimmable (Triac)
- Available also as wet location (see page 7)
- . Maximum run on a given lead is 60'
- Available in 60' and 120' reels.
- Cuttable in the field every 2"

ELECTRICAL

- 24VDC remote power supply required
- Rated at 1.5W per foot
- Rated life: 50,000 hrs.

OPTICS

- · 2700K, 3000K, 3500K, 4000K
- 120° viewing angle

CERTIFICATION

• ETL

WARRANTY

• 5 year warranty














DIAGRAM



GMEXT-24 Dry Location Series Tape will fit into the following mounting channels:

LED-CHL*

LED-CHL-D*

LED-CHL-XD

LED-CHL-XD-F

LED-CHL-45

LED-CHL-W

LED-CHL-BND*

Note: When using these channels, use only SureTite™ connectors.

* Use soldered lead for these channels See www.gmlighting.net

See www.gmlighting.ne for more information.

ORDERING INFORMATION

Catalog Number	Location	Length	Wattage	Lumens	CRI	Color Temp.*	LED Life
GMEXT-24-60-27	Dry	60'	1.5W / ft.	113 / ft.	90+	2700K	50,000 Hrs.
GMEXT-24-60-30	Dry	60'	1.5W / ft.	120 / ft.	90+	3000K	50,000 Hrs.
GMEXT-24-60-35	Dry	60'	1.5W / ft.	128 / ft.	90+	3500K	50,000 Hrs.
GMEXT-24-60-40	Dry	60'	1.5W / ft.	130 / ft.	90+	4000K	50,000 Hrs.
GMEXT-24-120-27	Dry	120'	1.5W / ft.	113 / ft.	90+	2700K	50,000 Hrs.
GMEXT-24-120-30	Dry	120'	1.5W / ft.	120 / ft.	90+	3000K	50,000 Hrs.
GMEXT-24-120-35	Dry	120'	1.5W / ft.	128 / ft.	90+	3500K	50,000 Hrs.
GMEXT-24-120-40	Dry	120'	1.5W / ft.	130 / ft.	90+	4000K	50,000 Hrs.

Each 60' reel comes with one 24" lead affixed at start of reel and three ESTW-60 connectors. Each 120' reel comes with two 24" leads affixed at each end of reel and four ESTW-60 connectors.

CONNECTORS

Catalog Number	Description
ESTC-1	Tape to tape SureTite [™] connector
ESTLK-60	60" tape to tape SureTite™ connector
ESTW-60	60" tape to power supply SureTite $^{\text{\tiny M}}$ connector



^{*} Kelvin temperature (color) ±100K