



P2RK

Product Images



Model: P2RK

Type: Horn Strobes; Outdoor

The SpectrAlert Advance P2RK is a red, two-wire, outdoor horn strobe with selectable strobe settings of 15, 15/75, 30, 75, 95, 110 and 115 cd. Outdoor back box included.

Product Documentation / Drawings

[Brochure: AV Products \(SAA O...](#)

[Brochure: AV Outdoor Products](#)

[Data Sheet: Outdoor Wall Horn...](#)

[Drawing Files: P2RK](#)

[Engineering Spec: Outdoor Hor...](#)

[Product Manual: Horns, Strobe...](#)

[More](#)

Accessories

Required

There are no required accessories for this product.

Optional



SA-WBB

The SpectrAlert Advance SA-WBB is a separate ship, wall-mount, outdoor back box.

Specifications

Candela	Selectable strobe settings of 15, 15/75, 30, 75, 95, 110 and 115 cd
Color	Red
DC Max Op Current	(see Data Sheet for complete current draw information)
FWR Max Op Current	(see Data Sheet for complete current draw information)
Location	Outdoor
Mounting	Wall
Operating Temperature	-40°F to 151°F (-40°C to 66°C)
Operating Voltage Range	8 to 17.5 V (12V nominal) or 16 to 33 V (24 nominal)
Outdoor Device Type	Horn Strobes

Series	SpectrAlert Advance
Voltage	Regulated 12DC/FWR or regulated 24DC/FWR
Wall Mount Dimensions	5.6"L x 4.7"W x 2.5"D (142 mm L x 119 mm W x 64 mm D)
Wall Mount with Box	5.7"L x 5.1"W x 2.0"D
Wiring Gauge	12 to 18 AWG

Agency Links

