



Philips LED
Reflector (Dimmable)

6W (50W)

E26
White
Dimmable

046677463618

Durable LED light with a focused bright beam

Avoid the hassle of changing lamps

This directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps

Application areas

- Perfect for accent lighting

Create a warm atmosphere

- Dimmable

Choose for high quality light

- Cool, energizing light

Specifications

Bulb characteristics

- Cap/fitting: E26
- Dimmable
- Shape: Reflector
- Voltage: 120 V
- Wattage: 6 W
- Wattage equivalent: 50 W

Bulb dimensions

- Height: 82.6 mm
- Width: 63.2 mm

Durability

- Number of switch cycles: 50000
- Lifetime of lamp: 25000 hour(s)
- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7

Light characteristics

- Beam angle: 35 degree
- Color: White
- Color rendering index (CRI): 80

- Color temperature: 3000 K
- Light output: 500 lumen
- Light effect/finish: White
- Warm-up time to 60% light: Instant full light
- Starting time: <0.5 s
- Rated center beam intensity: 1050 cd

Power consumption

- Light output [lumen value]: 500 lumen
- Power consumption per 1000h: 6 kW h

Other characteristics

- Mercury content: 0 mg
- Lamp current: 55 mA
- Power factor: 0.9

Rated values

- Rated lifetime: 25000 hour(s)
- Rated beam angle: 35 degree
- Rated luminous flux: 500 lumen
- Rated power: 6 W

Highlights

Dimmable



Designed to provide quality dimming to create the right ambiance for any activity, from relaxed to active atmospheres.

Cool, energizing light



This bulb has a color temperature of 3000K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Perfect for accent lighting

This LED spot light provides a focused beam of bright light, perfect for creating extra dimension and depth with accent lighting.

