


Home > Electrical > Lighting > LED Task Light

ZOOM

360 VIEW



LED Task Light

★★★★★[Write a review](#)[Ask a question](#)


1437SW

Southwire 1437 SlimLite LED Task Light features a high impact ABS body with an anti-roll design for added stability. Other features include an easy to find glow in the dark shield and an on - off switch control to use as an area or spot light. The long-lasting LEDs offer years of maintenance free operation. LED light and 0.5-watt top spot light has a 12-hour run time at 25--lumens (spot light only); 7-hour run time at 72 -lumens (Task Light) and 5-hour run time ay 97-lumens (spot light and task light together). This product features a non-slip rubbereze soft touch body and textured grip with a powerful co-planar, nickel plated neodymium and rare- earth magnet on the back. This light comes with (4) AAA Eveready batteries. Southwire 1437 SlimLite LED Task Light comes with a 1-year limited warranty that protects against defects in materials and workmanship. Southwire brand of timers and home controls bring simplicity to


☐ Add To Wishlist☐ Register

FEATURES	SPECIFICATIONS	DOWNLOADS
FEATURES		INCLUDES
<ul style="list-style-type: none">LED task light and 0.5-watt spot light12-hour run time at 25--lumens (spot light only); 7-hour run time at 72 -lumens (Task Light) and 5-hour run time ay 97-lumens (spot light and task light together)Non-slip Rubbereze soft touch body and textured gripComes with (4) AAA Eveready batteriesPowerful co-planar, nickel plated neodymium rare- earth magnet		

Featured Products



PL500
POLY LINE 500' 210 TENSILE STRENGTH



40140S
4-way Voltage Tester

Reviews

★★★★★
[Be the first to review this product](#)

Questions

[Be the first to ask a question](#)