
### **G**3 3" Miniature Line Voltage GU10 **Non-IC Housing**

#### LAMP WATTAGE: (1) MAXIMUM 120V 50W GU10



**DESIGNED FOR 2" X 6" JOIST CONSTRUCTION** 





VOLTAGE

WATTAGE



TRIM TYPE

G3 - ITEM SELECTOR: (Please check the boxes below for the option desired)

#### **Catalog Number:**

Project Name:

Note:

Type:

# elite и снти с

#### DESCRIPTION

Small aperture line voltage, thermally protected, specification grade recessed housing. For new construction. Non-insulated ceilings or where insulation can be kept 3" from the housing. Accommodates up to 50W GU10 lamps. Furnished with preinstalled adjustable bar hangers. Junction box is provided with four  $1\!\!\!/ 2"$  KOs, one  $3\!\!\!/ 4"$ KO and four Romex knockouts with strain relief.

#### **SPECIFICATION**

A. HOUSING - High temperature painted 22 gauge deep drawn single piece housing. Adjusts vertically in plaster frame to accommodate 1/2" to 1-3/8" ceiling. Accommodates lamps up to 50W depending on trim used.

B. SOCKET - GU10 floating socket allows for lamp to snap into trim and provide secure lamp retention.

C. BAR HANGERS - Preinstalled bar hangers allow housing to be positioned and locked at any point within a 24" joist span and can be shortened for 12" joists. They contain a double-headed real nail for secure attachment into the joist. Bar hanger nails are installed on a 20° downward angle for better contact, and the 90° pivoting mounting plate makes installation fast and accurate. Bar hangers can fit onto T-Bar spline with additional slots and holes for special mounting methods if necessary.

D. JUNCTION BOX - listed for through-branch cir-cuit wiring and has four 1/2" KOs, one 3/4" KO and four Ro-mex knockouts with true pry-out slots and strain clamps.

### **120V**



**GU10 SOCKET** 

#### FEATURES

- Thermally Protected Non-IC housing.
- Designed for accent and task lighting applications.
- · Wire through junction box.
- Preinstalled adjustable bar hanger.
- Dependable, favorable design and effortless installation.
- 5-1/2" height allows use in 2" x 6" joist construction.

· Special screw on the frame locks bar hangers in place which prevents the housing from any movement once installed.

#### OPTIONS

REFLECTOR TRIM RING MR 16 LENS FILTER

1. AIR-SHUT

- · Gasket to prevent air flow from heated or air conditioned spaces.
- · Meets all national air flow requirements.

G3	WATT VOLT	AGE OPTIC	DN TRIM TY	PE BAFFLE	REFLECTOR	TRIM/RING	FILTER (1)	FILTE	CP BZ	Copper Bronze	MB Black BZ Bronze CP Copper SN Satin Nickel SHZ Satin Haze	CP Copper CH Chrome PB Polish Brass BZ Bronze
Specification	15:					<b>1</b> = CH	- Chrome finished •	2 = SS - Stainle	W P	<b>E</b> White Black Satin Nickel	REFLECTOR CL Chrome RG Gold W White	TRIM/RING WH White BK Black SN Satin Nickel
		□ B1371 <sup>2</sup>	□ B1395	□ B1303								
		□ B1370 <sup>2</sup>	□ B1384	□ B1366								
		□ B1359 <sup>1</sup>	□ B1383	□ B1316	□ B1377		□ SHZ	CH <sup>1</sup>	BP8MR16-OR (Orange)		BP8MR16-UV (L	Jltraviolet)
		□ B1358 <sup>1</sup>	□ B1379	□ B1302	□ B1304		SN SN	□ BZ	BP8MR16-AM (Amber)		BP8MR16-CL (C	,
	AT (Air-Shut)	□ B1357 <sup>1</sup>	🗆 B1378	🗆 B1301	□ B1368		🗆 СР	🗆 РВ	BP8MR16-YE (Yellow)		BP8MR16-SOL	(Solite)
	OPTION	□ B1356 <sup>1</sup>	□ B1396	□ B1324	□ B1312	🗆 BZ	🗆 BZ	🗆 СН	BP8MR16-DL (Day Light)		BP8MR16-LI (Li	inear)
		□ B1355 <sup>1</sup>	□ B1376 <sup>2</sup>	□ B1325	□ B1352	CP	□ MB	CP	BP8MR16-PU (Purple)		BP8MR16-HC (F	,
		□ B1353	□ B1375 <sup>2</sup>	□ B1331	B1362				BP8MR16-PI (Pink)		BP8MR16-SF (S	. ,
□ 50W	120	□ B1351 <sup>1</sup> □ B1353 <sup>1</sup>	□ B1372 <sup>2</sup>	□ B1390 □ B1391	□ B1314 □ B1315	□ W □ P	CL RG	□ WH □ BK	BP8MR16-BL (Blue)		BP8MR16-FR (F BP8MR16-SP (S	,
	<b>—</b> 400											

BAFFLE

Sample of Catalog Number: G3-50W-B1301-W-WH-BP8MR16-BL



Submittal form is available @ www.iuseelite.com Tel: 323-888-1973 • Fax: 323-888-1977

SN CP CH PB Copper Chrome Polish Bras B7 n Nickel Bronze Haze \*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory.

Specifications and Dimensions subject to change without notice

REV: ELITE LIGHTING-SPEC-05-24-2011

## 3" **Low Voltage Trims**

( LAMP WATTAGE: 75W 12V MR16 / 50W 120V GU10 )

Catalog Number:	
-	
Project Name:	Туре:
Note:	

B1351CH RUBY I	B1353CH Ruby II	B1354CH Sapphire I	B1355CH Sapphire II		
0.D.:     3-7/8"       FINISH TRIM:     CH (CHROME)	0.D.: 3-7/8" FINISH TRIM: CH (CHROME)	0.D.: 3-7/8" FINISH TRIM: CH (CHROME)	0.D.: 3-7/8" FINISH TRIM: CH (CHROME)		
B1356CH EMERALD I	B1357CH Emerald II	B1358CH Topaz I	B1359CH Topaz II		
0.D.:     3-7/8"       FINISH TRIM:     CH (CHROME)			0.D.: 3-7/8" FINISH TRIM: CH (CHROME)		
B1360CH ONYX			B1372SS STAINLESS STEEL EYEBALL TRIM		
Real Provide P					
0.D.:     3-7/8"       FINISH TRIM:     CH (CHROME)	0.D.: 3-7/8" FINISH TRIM: SS (STAINLESS STEEL)	0.D.: 3-7/8" Finish Trim: SS (Stainless Steel)	0.D.: 3-7/8" FINISH TRIM: SS (STAINLESS STEEL)		
B1374SS Adj. Stainless steel square gimbal trim	B1375SS Stainless steel square eyeball trim	B1376SS Adj. Stainless steel square eyeball trim	B1396SN Square Baffle W/ Square Trim Ring		
0.D.: 3-7/8" FINISH TRIM: SS (STAINLESS STEEL)			<b>TRIM FINISH:</b> WH, BK, SN, CP, CH, PB, BZ		
Submittal form is available @ www.iuseelite.com Tel: 323-888-1973 • Fax: 323-888-1977Specifications and Dimensions subject to change without notice. REV: MAXILUME-SPEC-05-26-2011					

## 3" Low Voltage Trims

( LAMP WATTAGE: 75W 12V MR16 / 50W 120V GU10 )

Catalog Number:	
Project Name:	Туре:
	1360.
Note:	
NOLG.	

(LAMP WAI TAGE: <b>75W 12V MR16 / 50</b> V						
B1378SN-SN STEPPED BAFFLE (35° TILT)	B1379CL-WH REFLECTOR (35° TILT)	B1383WH SLOT APERTURE (35° TILT)	B1384P-WH Fully Adjustable W/ Baffle			
AVAILABLE COLOR COMBINATIONS: CP-CP, SN-SN, W-WH, P-WH, P-BK, BZ-BZ	AVAILABLE COLOR COMBINATIONS: CL-WH, CL-SN, RG-WH, MB-WH, W-WH, MB-BK, RG-PB, SN-SN, CL-CH, CP-CP, CP-WH, SN-WH	TRIM FINISH: WH, BK, SN, CP, CH, PB, BZ	(35° TILT, 359° ROTATION) AVAILABLE COLOR COMBINATIONS: W-WH, P-WH, P-BK, CP-CP, SN-SN, BZ-BZ			
B1380WH FULLY ADJUSTABLE (35° TILT, 359° ROT.)	B1391P-WH PINHOLE WITH BAFFLE	B1390WH-PEACH METROPOLITAN ICE LITE	B1395CL-SN SEMI-FROSTED SHOWER TRIM			
TRIM FINISH: WH, BK, SN, CP, CH, PB, BZ	AVAILABLE COLOR COMBINATIONS: CP-CP, SN-SN, W-WH, P-WH, P-BK, BZ-BZ	TRIM FINISH: WH, BK, SN, CP, CH, PB GLASS FINISH: BLUE, PEACH, GREEN, CLEAR, AMBER, FROSTED	REFLECTOR FINISH: CL RING FINISH: WH, BK, SN, CP, CH, PB, BZ			
B1301CP-CP STEPPED BAFFLE	B1302CP-WH REFLECTOR	B1316CL-WH REFLECTOR (35° TILT)	B1326CL-WH The Illuminator II			
AVAILABLE COLOR COMBINATIONS: CP-CP, SN-SN, W-WH, P-WH, P-BK, BZ-BZ	AVAILABLE COLOR COMBINATIONS: CP-CP, CP-WH, W-WH, RG-WH, SN-SN, SN-WH, MB-WH, CL-WH, MB-BK, RG-PB, CL-CH, CL-SN	AVAILABLE COLOR COMBINATIONS: CL-WH, CL-SN, CL-PB	AVAILABLE COLOR COMBINATIONS: CL-WH, CL-SN, CL-BK, MB-BK			
B1366CL-WH THE ILLUMINATOR	B1303WH SLOT APERTURE	B1314P-WH PINHOLE WITH BAFFLE	B1315RG-WH Pinhole with Reflector			
AVAILABLE COLOR COMBINATIONS: CL-WH, CL-SN, CL-BK, MB-BK	TRIM FINISH: WH, BK, SN, CP, CH, PB, BZ	AVAILABLE COLOR COMBINATIONS: CP-CP, SN-SN, W-WH, P-WH, P-BK, BZ-BZ	AVAILABLE COLOR COMBINATIONS: CL-WH, CL-SN, RG-WH, MB-WH, W-WH, CP-CP			

# elite

Submittal form is available @ www.iuseelite.com Tel: 323-888-1973 • Fax: 323-888-1977 Specifications and Dimensions subject to change without notice. **REV:** <u>MAXILUME-SPEC-05-26-2011</u>

## 3" **Low Voltage Trims**

( LAMP WATTAGE: 75W 12V MR16 / 50W 120V GU10 )

Catalog Number:	
0	
Project Name:	Туре:
Note:	

B1362WH Shower Trim W/ Frosted Lens	B1352CL-WH Shower Trim with Reflector	B1368W-WH Fully Adjustable W/ Baffle (35° Tilt)	B1312SN FULLY ADJUSTABLE (35° TILT)		
TRIM FINISH: WH, BK, SN, CP, CH, PB, BZ	AVAILABLE COLOR COMBINATIONS: CL-WH, CL-CH, RG-WH, RG-PB	AVAILABLE COLOR COMBINATIONS: CP-CP, SN-SN, W-WH, P-WH, P-BK	<b>TRIM FINISH:</b> WH, BK, SN, CP, CH, PB, BZ		
B1304W-WH EYEBALL W/ BAFFLE (47° TILT)	B1377CL-WH CROSSBLADE REFLECTOR	B1320WH-CRYSTAL Metropolitan Moon Lite	B1325WH-AMBER METROPOLITAN STEP LITE		
AVAILABLE COLOR COMBINATIONS: CP-CP, SN-SN, W-WH, P-WH, P-BK	AVAILABLE COLOR COMBINATION: CL-WH	RING FINISH: WH GLASS FINISH: GREEN, BLUE, AMBER, PEACH, FROSTED, CRYSTAL	RING FINISH: WH GLASS FINISH: GREEN, BLUE, AMBER, PEACH, FROSTED, CRYSTAL		
B1324WH-RED Metropolitan Honey Lite					
RING FINISH: WH GLASS FINISH: GREEN, BLUE, AMBER, PEACH, FROSTED, CRYSTAL	W White CL Chrome WH   P Black RG Gold BK   SN Satin Nickel W White SN   CP Copper MB Black CP   BZ Bronze CP Copper CH   SN Satin Nickel PB SN Satin Nickel	Satin Nickel Copper Chrome Polish Brass Bronze			

\*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory.



Submittal form is available @ www.iuseelite.com Tel: 323-888-1973 • Fax: 323-888-1977

Specifications and Dimensions subject to change without notice.