

### M12™ ROCKET™ Dual Power **Tower Light**

2132-20 Tool-Only

### Specifications:

Lumens	1,400 / 700
Modes	High, Low
Powered By	M12 <sup>™</sup> or Corded
Height	30.5" Collapsed, 5' 8" Fully Extended
Weight	6.7 lbs

Battery and Charger Sold Separately



# M12™ ROVER™ Mounting Flood Light

2364-20 Tool-Only

# **Specifications:**

	-	
	Lumens	1,000 / 400 / 200
	Modes	High, Medium, Low
	Hands Free	Integrated Magnet, Spring Loaded Clamp
	Water & Dust Rating	IP54
	Length / Weight	7.5" / 2.2 lbs

Battery and Charger Sold Separately



# M12™ Metal Flashlight Kit 2355-21 (2355-20 Tool-Only)

Smanification

Specifications:	
Lumens	800 / 325 / 800
Modes	High, Medium, Strobe
Beam Distance	375 yd / 343 m
Beam Focus	Slide, Spot/Flood
Water & Dust Rating	IP54
Structure	6000 Series Aluminum, Type II Anodize Finish
Length / Weight	9.0" / 1.2 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Lanyard, Charger

# M12™ Spot Light

2353-20 Tool-Only

# **Specifications:**

Lumens	750 / 400 / 750
Modes	High, Low, Strobe
Beam Distance	700 yd / 640 m
Water & Dust Rating	IP54
Length / Weight	6.1" / 1.4 lbs

Battery and Charger Sold Separately

Includes: Lanyard



**POWERED BY** 

# M12™ Lantern/Flood Light

2362-20 Tool-Only

#### Specifications

Specifications:	
Lumens	400 / 200 / 40 / 400
Modes	High, Medium, Low, Strobe
Beam Pattern	Adjustable 180° – 360°
Water & Dust Rating	IP54
Hands-Free	2 Hooks for Hanging
USB Charger	2.1A USB Charging Port for External Devices
Length / Weight	10.5" / 1.0 lb

Battery and Charger Sold Separately



M12™ Underhood Light Kit 2125-21XC (2125-20 Tool-Only)

# Specifications:

Lumens	1,350 / 600
Modes	High, Low
Hooks	FINISHGUARD™ to Resist Wear & Provide Lasting Protection
Length / Weight	48" Collapsed, 78" Fully Extended / 2.2 lbs

Includes: (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, Charger

# M12™ Stick Light

2351-20 Tool-Only

# **Specifications:**

Lumens	220
Hands-Free	Multi-Position Stainless Steel Hook
Water & Dust Rating	IP54
Length / Weight	9.3" / 0.6 lbs

Battery and Charger Sold Separately

Related Accessory: 49-24-2351 M12™ Stick Light Magnet Holds light to metal surfaces for hands-free use

# M12™ Work Light

49-24-0146 Tool-Only

# **Specifications:**

Battery and Charger Sold Separately





# M12™ Heated TOUGHSHELL **Jacket Kit**

Black 202B-21 (S - 3X)\* 202B-20 Jacket-Only Red 202R-21 (S - 3X)\* 202R-20 Jacket-Only

# **Specifications:**

Heat Zones	3 (Chest, Back, Pockets)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	TOUGHSHELL™ Stretch Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source

### M12™ Heated QUIETSHELL **Jacket Kit**

Camo 222C-21 (S - 3X)\* 222C-20 Jacket-Only

# **Specifications:**

	Heat Zones	3 (Chest, Back, Pockets)
	Heat Settings	3 (High, Medium, Low)
	Run-Time	Up to 8 Hours
	Outer Material	QUIETSHELL Stretch Polyester
\	Wind / Water Resistant	Yes
/	Washer / Dryer Safe	Yes

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source

### M12™ Heated AXIS™ **Jacket Kit**

Black 203B-21 (S - 3X)\* 203B-20 Jacket-Only

Washer / Dryer Safe

#### **Specifications:** Heat Zones 3 (Chest. Back. Shoulders Heat Settings 3 (High, Medium, Low) Run-Time Up to 8 Hours AXIS™ Ripstop Polyester Outer Material Wind / Water Resistant Yes

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source

## M12™ Women's Heated AXIS™ **Jacket Kit**

Black 233B-21 (S - 2X)\* 233B-20 Jacket-Only

# **Specifications:**

_	
Heat Zones	3 (Chest, Back, Shoulders)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	AXIS™ Ripstop Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Pack, Micro-USB 3 ft Cable and Wall Plug, M12™ Compact Charger and Power Source



# M12™ Heated Hoodie Kit

Black 302B-21 (S - 3X)\* 302B-20 Hoodie-Only Gray 302G-21 (S - 3X)\* 302G-20 Hoodie-Only Red 302R-21 (S - 3X)\* 302R-20 Hoodie-Only

# **Specifications:**

-	
Heat Zones	2 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Wind Resistant	Yes
Washer / Dryer Safe	Yes

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, M12™ Battery Holder, Charger



202B-21S = M12<sup>™</sup> Heated TOUGHSHELL<sup>™</sup> Black Jacket Kit in Small