

# MasterClass LED candles

Philips LED dimmable candles and decorative lamps incorporate a revolutionary new shaped prism that allows the optics to radiate brilliant, clear and sparkling white LED light. The light quality provides consistent color from every angle – even when dimmed in the most intimate of light levels.

- Lowers maintenance costs by reducing re-lamp frequency
- Contains no mercury
- Up to 90 CRI options available

## MasterClass LED decorative

Ordering, electrical and technical data (Subject to change without notice)



E12 E26

Product Number	12NC	Description	Watts (W)	Lumens (lm)	Volts	CRI	Life <sup>2</sup> (Hrs)	Color Temp (K)	Material	Finish	Legend	Estimated Release Date	
<b>Candles 25W equivalent lamps dimming</b>													
W	549329	929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	2	180	120	90	15,000	2700-2200	Glass	Clear	F	Q3
W	549246	929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	2	180	120	90	15,000	2700-2200	Glass	Clear	G	Q3
<b>Candles 40W equivalent lamps dimming</b>													
W	537613	929001951153	4.5BA11/VIN/820/E12/CL/GL/DIM 4/1BC T20	4.5	300	120	80	15,000	2000	Glass	Amber	E	
W	549568	929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	3.3	300	120	90	15,000	2700-2200	Glass	Clear	F	Q3
W	549584	929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	3.3	300	120	90	15,000	2700-2200	Glass	Clear	H	Q3
W	549543	929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	3.3	300	120	90	15,000	2700-2200	Glass	Clear	G	Q3
W	549550	929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	3.3	300	120	90	15,000	2700-2200	Glass	Clear	H	Q3
D	457127	929001167004	4.5B12/LED/827-22/E12/DIM 120V	4.5	330	120	80	25,000	2700-2200	Glass	Clear	A	
D	457192	929001167304	4.5B12/LED/827-22/E26/DIM120V	4.5	330	120	80	25,000	2700-2200	Glass	Clear	B	
D	457218	929001167104	4.5BA12/LED/827-22/E12/DIM 120V	4.5	330	120	80	25,000	2700-2200	Glass	Clear	C	
D	458182	929001179104	4.5BA12/LED/827-22/E26/DIM 120V	4.5	330	120	80	25,000	2700-2200	Glass	Clear	D	
<b>Candles 60W equivalent lamps dimming</b>													
W	549337	929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	5.5	500	120	90	15,000	2700-2200	Glass	Clear	F	Q3
W	549345	929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	5.5	500	120	90	15,000	2700-2200	Glass	Clear	H	Q3
W	550250	929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	5.5	500	120	90	15,000	2700-2200	Glass	Clear	G	Q3
W	549576	929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	5.5	500	120	90	15,000	2700-2200	Glass	Clear	I	Q3
D	458695	929001182004	7B12/LED/827-22/E12/DIM 120V	7	500	120	80	25,000	2700-2200	Glass	Clear	A	
D	458661	929001182104	7B12/LED/827-22/E26/DIM 120V	7	500	120	80	25,000	2700-2200	Glass	Clear	B	
D	458638	929001182204	7F15/LED/827-22/E26/DIM 120V	7	500	120	80	25,000	2700-2200	Glass	Clear	M	
W	547959	929002091503	5.5F15/PER/927-922/CL/G/E26/WGX 1BC	5.5	500	120	90	15,000	2700-2200	Glass	Clear	J	