

6EP19312DC31 | 6EP19312DC31



SITOP Module 24 V USC DC /6 A Uninterrupted Power supply With serial interface input: 24 V DC/6.85 A output: 24 V DC/6 A

List Price [Show prices](#)

Customer Price [Show prices](#)

Service & Support (Manuals, Certificates, FAQs...) [Download](#)

Accessory (4)



6EP19356MD11

SITOP rechargeable battery module 24 V/3.2 Ah with maintenance free Sealed lead batteries for...



6EP19356MD31

SITOP pure lead battery module 24 V/2.5 Ah with maintenance free Sealed lead batteries for SITOP...



6EP19356ME21

SITOP Akkumodul 24 V/7 Ah with maintenance free Sealed lead batteries for SITOP DC-USV Module ...



6EP19356MF01

SITOP rechargeable battery module 24 V/12 Ah with maintenance free Sealed lead batteries for...

Product

Article Number (Market Facing Number)	6EP19312DC31 6EP19312DC31
Product Description	SITOP Module 24 V USC DC /6 A Uninterrupted Power supply With serial interface input: 24 V DC/6.85 A output: 24 V DC/6 A
Product family	SITOP DC UPS
Product Lifecycle (PLM)	PM300:Active Product

Price data

Price Group	684
List Price	Show prices
Customer Price	Show prices
Metal Factor	None

Delivery information

Export Control Regulations	AL : N / ECCN : N
Standard lead time ex-works	1 Day/Days
Net Weight (lb)	0.992 lb
Product Dimensions (W x L x H)	Not available
Packaging Dimension	5.512 x 5.512 x 2.362
Package size unit of measure	in
Quantity Unit	1 Piece
Packaging Quantity	1

Additional Product Information

EAN	4025515151029
UPC	662643297997
Commodity Code	85049099
LKZ_FDB/ CatalogID	KT10-PD
Product Group	4215
Country of origin	Austria
Compliance with the substance restrictions according to RoHS directive	Since: 08/01/2006
Returnable	Yes
WEEE (2012/19/EU) Take-Back Obligation	Yes
REACH Art. 33 Duty of Information	

Classifications

	Version	Classification
eClass	6	27-04-06-90
eClass	7.1	27-04-06-90
eClass	8	27-04-06-90
eClass	9	27-04-07-05
eClass	9.1	27-04-07-05
ETIM	4	EC000382
ETIM	5	EC000382
ETIM	6	EC000382
ETIM	7	EC000382
IDEA	4	4149
UNSPSC	14	39-12-10-26
UNSPSC	15	39-12-10-11