OCTAGON CEILING BOX



- Superior mounting methods to accommodate screws and/or nail installation. The box provides flexibility by offering universal mounting brackets, with screw and nail guides.
- Ground screw spacing positioned in line with wire entry. Easy to wrap ground wires with fingers or pliers.
- Advanced overmoulded ground strap retention for better support.
- A full 'u' shaped ground strap that improves mechanical performance and continuous ground.
- Engineered with pre-installed device mounting screws 2 of 8 32" x 1" allows quicker installations.
- Bottom ground screw location complete with two green ground screws to accommodate quick installation.

• Large cubic capacity – 27" cubic capacity allows ease to terminate and accommodate conductors, wire nuts and grounding.

B1

NON-METALLIC BOXES

- Centering V notches saves installation time by assuring consistent proper box positioning.
- 4 oversize ½" drywall breakaway tabs with score lines.
- 2 x 45° mounting holes are located inside and closed off giving the installer more mounting options.
- Star shape openings to secure and hold screws or nails in place while working overhead.

HUBBELL



NON-METALLIC BOXES



APPLICATION

Accommodates wiring devices such as switches and receptacles.

PRODUCT FEATURES

• Self-clamping wire entry tabs

STANDARD MATERIAL

Molded from high-strength plastic resin •









2001R

2021R





2016R



2014R

CATALOGUE NUMBER	CAPACITY (CU. IN)	DESCRIPTION	CABLE CLAMPS			
Device Boxes - For use with non-metallic sheathed cable						
2001R	18.0	1-gang with flush bracket, 1/2" setback	4			
2021R	18.0	1-gang with compact mounting bracket, 1/2" setback	4			
2002R	37.0	2-gang with flush bracket, 1/2" setback	8			
2003R	54.0	3-gang with flush bracket, 1/2" setback	12			
4" Round Ceiling Box - For use with non-metallic sheathed cable						
2027R*	27.0	Round box with flush bracket, 1/2" setback	4			
Stove/Dryer Box - For use with non-metallic sheathed cable						
2006R	42.0	stove/dryer box, 1/2" setback	1/2"(2), 3/4"(1)			
Trailer Box - For use with non-metallic sheathed cable						
2016R	17.0	1-gang, Trailer Box	2014R			
2014R	-	Fast Wire Clamp for Trailer Box -				

*Patent Pending

B2

trade**SELECT**



NON-METALLIC BOXES

B3

APPLICATION

Vapour barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment from elements outside of the structure. Accommodates wiring devices such as switches and receptacles.

PRODUCT FEATURES

- Self-clamping wire entry tabs
- Vapour/air barrier flange and integral wire entry seal provides superior energy savings and quick installation.

STANDARD MATERIAL

• Molded from high-strength plastic resin.





2011FBAR

2002FBAR

2003FBAR





2006FBAR

CATALOGUE NUMBER		CAPACITY (CU. IN)	DESCRIPTION	CABLE CLAMPS		
Device Boxes - For use with non-metallic sheathed cable						
Flanged w/ Vapour Barrier	Flanged Only					
2011FBAR	2011F	18.0	1-gang with flush bracket, 1/2" setback	4		
2002FBAR	2002F	37.0	2-gang with flush bracket, 1/2" setback	8		
2003FBAR	2003F	54.0	3-gang with flush bracket, 1/2" setback	12		
4" Round Ceiling Box - For use with non-metallic sheathed cable						
Flanged w/ Vapour Barrier	Flanged Only					
2027FBAR*	2027F*	27.0	Round box with flush bracket, 1/2" setback	4		
Stove/Dryer Box - For use with non-metallic sheathed cable						
Flanged w/ Vapour Barrier	Flanged Only					
2006FBAR	2006F	42.0	stove/dryer box, 1/2" setback	1/2"(2), 3/4"(1)		

*Patent Pending



B4

trade**SELECT**[™]