



- Flush or surface mount enclosure (hardware provided)
- Hinged cover can be mounted to swing from either side
- Integral trim ring hides rough-in hole in except NSOBOX48 sheet rock providing a finished appearance
- Horizontal and vertical module mounting holes for maximum flexibility
- Unique 89D bracket mounting holes allow easy mounting of 66 blocks and peripherals
- Provisions to mount optional duplex power and lock kit available
- Integral cable management slots and tie-wraps provided to help dress cable runs
- Additional nylon push pins provided to assist module mounting
- Material: 20-18 gauge steel
- Finish: white, powder coat
- UL and cULus Listed 1863

Network Enclosures

Description		Number of Module Placement	Catalog Number
Pre-configured Network System Basic home network kit includes: One box with hinged cover NSOBOX14, One primary 8-port telephone module NSOPTM8, One four way coaxial splitter module NSOVDM4		—	NSOBNK14
10 Inch Network Enclosure for MDU and Modular Applications Dimensions: 14.38 in. W x 10.0 in. H x 3.96 in. D Knock-outs: Top: four 1½ in. N.P.T. or completely open combo; Bottom: four 1½ in. N.P.T. or completely open combo; Back: none	with Hinged Cover with Panel Cover 10"H Box only Hinged Door Panel Cover	3	NSOBOX10 NSOBOX10BC NSOBOX10B NSOBOX10D NSOBOX10C
14 Inch Network Enclosure Dimensions: 14.38 in. W x 14 in. H x 3.96 in. D Knock-outs: Top: two 1 in. Dia. and three 1½ in. N.P.T. combo; Bottom: one 1 in. Dia. and one 1½ in. N.P.T. combo; Back: two ¾ in. N.P.T.	with Hinged Cover with Panel Cover 14"H Box only Hinged Door Vertical Door Panel Cover 2"D Extension Bracket with ventilation and WiFi KOs	5	NSOBOX14 NSOBOX14BC NSOBOX14B NSOBOX14D NSOBOX14DL NSOBOX14C NSOBOX14X2
28 Inch Network Enclosure Dimensions: 14.38 in. W x 28 in. H x 3.96 in. D Knock-outs: Top: five 1½ in. N.P.T.; Bottom: two power kit knockouts; Back: four ¾ in. N.P.T.	with Hinged Cover with Panel Cover 28"H Box only Hinged Door Vertical Door* Panel Cover 2"D Extension Bracket with ventilation and WiFi KOs	11	NSOBOX28 NSOBOX28BC NSOBOX28B NSOBOX28D NSOBOX28DL NSOBOX28C NSOBOX28X2
48 Inch Network Enclosure Dimensions: 14.38 in. W x 48 in. H x 3.96 in. D Knock-outs: Top: five 1½ in. N.P.T.; Bottom: two power kit knockouts; Back: none	with Hinged Cover	21	NSOBOX48



NSOBOX10



NSOBOX14



NSOBOX28

Note: For custom installs, REKHS is also available. See section P for ordering information.
* Door covers rough-in, no trim ring provided.