



PLUGTAIL® SINGLE POLE 15 AMP TOGGLE SWITCH, BROWN

PT15AC1 | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Single Pole Toggle Switch, 15amp 120/277vac, Brown

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.
- Impact- and chemical- resistant cover.
- Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.
- One-piece nickel-plated mounting strap for superior corrosion resistance.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Auto-ground clip assures positive ground.
- Shallow design for easier installation.
- Heavy-duty bumpers for quiet, smooth operation.
- No exposed terminals create a finger-safe application before, during, and after installation.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Brown
Product Series: PlugTail
Type: Toggle
Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111
CSA Standard: Yes
cULus: Yes
Federal Spec: Yes
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"

Height (US): 3.281"

Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

Grade Type: Specification

COUNTRY OF ORIGIN

Country Of Origin: MEXICO