

## Selective Call Intercom Video Door Unit, Oil-Rubbed Bronze

IC5003-OB



This innovative door unit, housed in an attractive weatherproof finish, includes a wide-angle color camera for front door monitoring. When integrated with the On-Q camera system LCD, the doorbell press enables the image from the door unit camera to appear on the LCD screen. The image can also appear on any TV connected to a TV display port.

### features & benefits

- Crisp color image also performs well in low-light conditions.
- Includes up to 20 digital door tones.
- As part of the [Studio collection](#) this innovative video door unit enhances the curb appeal of any home.
- Installs in a standard double gang opening with simple RJ45 plug design for easy installation and troubleshooting.

### specifications

## General Info

Color: Oil Rubbed Bronze

## Construction Information

spec1: Power Requirements

## Dimensions

Overall Dimensions U S: 5.1" H x 4.5" W x 1.8" D

Product Weight U S: 1.5 lbs

Weight: 1.5 lb

## Cord Information

Pinning:

Pin 1 24 VDC Out

Pin 2 GND

Pin 3 Audio (+)

Pin 4 COMMA

Pin 5 COMMB

Pin 6 Audio (-)

Pin 7 VIDEO  
INPUT

Pin 8 GND

## Technical Information

Cat5 Cable Rating: CAT5 UTP, 4 pair solid conductor (24 AWG)

Firmware Update: 16 Pin Header Connector

Humidity: Up to 90% RH (non-condensing)

Material: Cast; Zinc Alloy

Operating Temperature Celsius: -25 to 55 degrees

Operating Temperature Fahrenheit: -13 to 131 degrees

Power Requirements: +24Vdc, +/-1.5Vdc, 0.15A max

Q Link Selective Call Ports: RJ-45

Storage Temperature: -45 to 85°C (-49 to 185°F)

Viewing Angle: Horizontal: 105 degrees; Vertical: 80 degrees