



IN-WALL REMOTE RF DIMMER, WHITE

LC2103-WH | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

The Remote RF Dimmer provides convenient control from multiple access points when used with a load-bearing RF dimmer (LC2101, LC2102, LC2150). Legrand's RF Lighting Control switches and dimmers also integrate with the Intuity home automation system by Legrand for unified control of lights, security, audio, and more.

radiant® Screwless Wall Plate not included.

Check out the [RF Lighting Control mobile app](#).

- Part of the radiant® collection.
- Provides convenient control from multiple access points or mobile app
- Easy-to-install with a home's existing wiring
- Integrates with Legrand's [intuity](#) and [third party](#) home automation systems
- Integrates with Legrand's Intuity Home Intelligence
- Patented 900 MHz communication protocol. Avoids interference with other devices, such as cordless phones and baby monitors.
- Fully compatible with the [adorne®](#) Wi-Fi Ready lighting control devices
- Available in white, light almond and nickel colors
- Voice activated control with Google Assistant and Amazon Alexa

SPECIFICATIONS

GENERAL INFO

Color: White

Size: Unit Package: 4.8" x 3.03" x 2.48"

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

UL Standard: Yes

CONSTRUCTION INFORMATION

Component 4: 80442803275

DIMENSIONS

Depth (Metric): 121.92mm

Depth (US): 4.8"

Height (Metric): 62.99 mm

Height (US): 2.48"

Width (Metric): 76.96 mm

Width (US): 3.03"

Weight: 0.31 lbs

TECHNICAL INFORMATION

AC Voltage Input: 120V

Frequency: 900 MHz

Humidity: 0-90% relative humidity, non-condensing

Interoperability: Top Dog™ RF Communication Protocol

Mounting: Standard electrical box

Operating Temperature (Celsius): 0°C to 43°C