

24VDC 30W Power Supply

PW1030



Provides power for the Selective Call Intercom Module.

features & benefits

24 volt, 30 watt power supply.

specifications

General Info

Type: Power Supply

Listing Agencies/Third Party Information

cULus: Yes
FCC Standard: Yes
UN SPS C: 39121006

Dimensions

Height Metric: 31 mm
Height U S: 1.22"
Length U S: 3.86"
Length Metric: 98 mm
Width Metric: 45mm
Width U S: 1.77 in

Technical Information

AC Voltage Input: 115V/60Hz and 230V/50Hz
Amps: 1.5
Efficiency: 0.82
Humidity: 10% to 90% Humidity
Operating Temperature Celsius: 0°C to 40°C
Operating Temperature Fahrenheit: 32°F to 104°F
Volts D C: 24 VDC
Watts: 30 W
Receptacle Type: DC Barrel Jack
Number Of Receptacles: 1