
4-WAY VERTICAL COAX SPLITTER (2 GHZ)

VM0204 |



FEATURES & BENEFITS

This splitter is designed to be specified into an EN0800 enclosure for basic structured wiring applications, such as multi-dwelling units and small homes.



- Package includes one 4-way 2 GHz coax splitter

SPECIFICATIONS

GENERAL INFO

Finish: Nickel-Plated with Tin Sealed
Number Of Ports: 4
Size: 1.62" x 2.91" x 1.22"
Connection Type: F-Connector, female
Type: Low Voltage, Coax Splitter, Single-Bay
Special Features: 4-way Vertical Splitter
Style: Single-Bay Module

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (US): 1.22"
Height (US): 1.62"
Width (US): 2.91"
Rack Units: Custom MDU enclosure mountable

TECHNICAL INFORMATION

Frequency: Bandwidth: 1000~2050 MHz

Material: Cast Alloy

Supported Standards: RoHS

Typical Insertion Loss: Insertion Loss: 10.5 dB max

Typical Return Loss: Return Loss, Input: 15 dB min; Return Loss, Output: 12 dB min