

RT-50 Preset Countdown Time Switch

Pushbutton switch for automatic-off control

Easy operation and precise time countdown

Lighted switch for visibility in darkened rooms



Ideal for closets, laundry rooms, pantries and storage areas

 Choice of six preset on-times from 1 minute to 60 minutes

PROJECT

LOCATION/TYPE

Product Overview

Description

The RT-50 Preset Countdown Time Switch automatically turns lighting or other loads off when the selected on-time expires. It replaces standard single-pole wall switches for energy savings throughout a range of applications.

Operation

Users press one of the six preset buttons to turn connected lighting on for the corresponding period of time. After the time has elapsed, lighting is automatically turned off. Lights can be turned off before the countdown is complete by pressing the on/off button. Users may press the on/off button to turn lights on. The time switch will activate the preset that was last used, and the indicator light for that preset will turn on. To change the countdown, users press the desired preset button and the RT-50 will reset to that countdown interval.

Choice of On Times

The RT-50 will keep lighting on for 1, 5, 10, 20, 30 or 60 minutes. The digital on-time options provide precise control and help users avoid leaving lights on unnecessarily.

Applications

Countdown time switches are an ideal lighting control choice for areas where wall switch vacancy or occupancy sensors may be inappropriate. The RT-50 preset time switch is recommended for controlling lighting in areas such as closets, laundry rooms, pantries and storage rooms.

Features

- Seven-button preset time switch
- Replaces single-pole switch
- Selectable on-time: 1, 5, 10, 20, 30, 60 minutes
- Lighted switch for visibility in darkened rooms
- Low-profile styling
- Choice of five decorator colors

- · Operates most common types of lighting
- · Relay-based switching
- Zero crossing reduces stress on the relay and increases product longevity
- No current leakage to load in off mode for safety
- Compatible with decorator wall plates




Specifications

- 120 VAC, 60 Hz; neutral required
- Load ratings: 0-600W incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low voltage (MLV), electronic low voltage (ELV), and 1/6 Hp motor
- On-time options: 1, 5, 10, 20, 30, 60 minutes
- 2.63" x 1.69" x 1.88" (67.8mm x 42.9mm x 47.8mm) L x W x D
- Operating conditions: 32-131°F (0-55°C), 95% RH, non-condensing; for indoor use only
- UL and cUL listed
- Five year warranty


Installation & Wiring

Wiring Diagram



Controls

Product Controls



Ordering Information

Catalog No.	Color	Description	Voltage	Load Rating
RT-50-W	White	Preset Countdown	120 VAC; 60 Hz	0-600W incandescent, LED,
RT-50-I	lvory	Time Switch		fluorescent, CFL, MLV, ELV,
RT-50-LA	Lt. Almond			1/6 Hp motor
☐ RT-50-A	Almond			
☐ RT-50-B	Black			

Order wall plate separately.