



LS SERIES INCANDESCENT SLIDE DIMMER, IVORY

LS603PI | [Pass & Seymour](#)

FEATURES & BENEFITS

Incandescent Slide Dimmer, Preset 3way 600w, Ivory



- Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.
- Electromagnetic and radio-frequency interference protection built in.
- Sleek, sculpted contemporary design. No dirt-catching crevices.
- Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.
- Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.
- Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.
- Superior heat management.
- No derating on 600W units.
- Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Product Series: LS
Type: Incandescent
Number Of Poles: 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No

CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121502
UR: No

DIMENSIONS

Depth (US): 1.28"
Height (US): 4.19"
Width (US): 1.74"

TECHNICAL INFORMATION

Volts: 120V
Watts: 600

COUNTRY OF ORIGIN

Country Of Origin: CHINA