

## 20GB612 Steel Plugmold® Multioutlet System

V20GB612, G20GB612



6' Plugmold® Multioutlet System with 6 single outlets



### features & benefits

- **Steel Raceway.** Provides superior strength for any dry location installation.
- **Compact, low profile appearance.** Requires minimal space.
- **Available in Ivory ScuffCoat or gray baked enamel finish.** The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.
- **Full range of fittings.** Provides a complete wiring solution.
- **Single-and-dual-gang boxes.** Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.
- **Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover.** Ideal for short runs requiring additional outlets in electrically busy areas.
- **Single, alternating circuit, and isolated ground receptacles.** Meets virtually any job requirement.
- **Choice of receptacle spacing.** Center spacing between receptacles of 6", 9", 12", and 18".
- **Snapicoil harnesses of prewired receptacles in 48' and 50'.** Eliminates multiple splicing, speeding up installation on long runs.
- **Snapicoil harnesses offer a choice of receptacle spacing.** Center spacing between receptacles of 12", 18" and 30".
- **Customization available.** All products can be modified to accommodate virtually any application.

### specifications

**General Info**

Product Series: 2000  
Component Type: Raceway Base & Cover

**Technical Information**

Material: Steel  
Capacity: Single-Channel

**Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA  
Buy American Act Status: Buy American Act Compliant