

---

## 15 AMP NEMA L515 PLUG - YELLOW BACK, WHITE FRONT BODY, CORROSION- RESISTANT

CRL515P | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### Turnlok Plug 3wire 15amp 125volt Corrosion Resistant

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow, White

Type: Plug

Number Of Wires: 3

Special Features: Corrosion-Resistant

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

#### DIMENSIONS

Diameter (US): 1.516"

Length (US): 2.617"

**TECHNICAL INFORMATION**

Amps: 15A

NEMA Configuration Number: L515

Volts: 125V

Volts (AC): 125

**COUNTRY OF ORIGIN**

Country Of Origin: MEXICO