

# 15A, 120/125V Decorator Combination Single-Pole Switch & Single Receptacle, White

681W



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.



## features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

## specifications

### General Info

Color: White  
Type: Standard  
Number Of Poles: 1  
Style: Decorator

### Listing Agencies/Third Party Information

UL Listing No: 20, 498  
UL Standard: Yes  
UN SPS C: 39121406

### Dimensions

Depth U S: 1.2"  
Height U S: 3.812"

Width U S: 1.313"

#### **Technical Information**

Amps: 15

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 120/125

#### **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant