

# 15W47 Watertight Rubber Housing Connector, Yellow

15W47



Straight Blade Watertight Connector, 15amp 125volt, 5-15R Configuration, Multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.



## features & benefits

- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Compression-type cord grip provides watertight seal and 205 lb. pull out strength.
- Multiple ring seals between plug and connector ensures protection from water and contaminants.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- NEMA 4, 4X, Watertight. IP65, 66, 67. Rated watertight for 1,000 psi high-pressure hose-down.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: yellow  
Type: Connector  
Features: Watertight  
Number Of Poles: 2 Pole  
Number Of Wires: 3 Wire

Special Features: Watertight,NEMA

### **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes

UL Listing No: E146159

UL Standard: Yes

UN SPS C: 39121402

### **Dimensions**

Diameter U S: 1.81"

Length U S: 4.01"

### **Technical Information**

Amps: 15 Amp

NEMA Configuration Number: 5-15R

NEMA Rating: 4X/6P

Volts: 125V

Volts A C: 125

### **Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA

Buy American Act Status: Buy American Act Compliant