

# Hard Use Specification Grade Switch, Ivory

CSB20AC4I



Construction 4way Switch, Back & Side  
Wire, 20amp 120/277volt, Ivory.



## features & benefits

- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

**General Info**

Color: Ivory  
Duty: Hard Use  
Number Of Poles: 4-way

**Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WS896  
UL Listing No: 20  
UL Standard: Yes  
UN SPS C: 39121507

**Dimensions**

Depth U S: 1.073"  
Height U S: 3.281"  
Width U S: 1.320"

**Technical Information**

Amps: 20 Amp  
Volts: 120/277VAC  
Volts A C: 120/277  
Grade Type: Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant