

# Tamper-Resistant Hospital Grade Receptacles, Back & Side Wire, 15A, 125V, Brown

TR62H



Tamper-Resistant Hospital Grade Duplex Receptacle, Back & Side Wire, 15amp 125volt, Brown



## features & benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: brown

Type: Receptacles  
Special Features: Tamper-Resistant,back, side wire

### **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406  
UR: No

### **Dimensions**

Depth U S: 0.9"  
Height U S: 3.281"  
Width U S: 1.625"

### **Technical Information**

Amps: 15 Amp  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Hospital

### **Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant