



## INDUSTRIAL EXTRA HEAVY-DUTY SPECIFICATION GRADE SWITCH, GRAY

PS20AC3GRY | [Pass & Seymour](#)

### FEATURES & BENEFITS

3way Toggle Switch, Back & Side Wire, 20amp 120/277volt, Gray



- One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.
- Impact- and chemical-resistant cover.
- Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.
- One-piece nickel-plated brass strap for superior corrosion-resistance.
- Auto-ground clip assures positive ground.
- Cam control and spring actuator for positive "makes and breaks."
- Heavy-duty bumpers for quiet, smooth operation.
- Locking support provides resistance to face and back body separation.
- Oversized silver-alloy contacts for long life and better heat dissipation.
- Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.
- Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.
- Grounding terminal is standard with screw-pressure plate back wire.
- Shallow design for easier installation.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Type: Toggle  
Duty: Extra Heavy Duty  
Number Of Poles: 3-way

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

## DIMENSIONS

Depth (US): 1.073"  
Height (US): 3.281"  
Width (US): 1.320"

## TECHNICAL INFORMATION

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277  
Grade Type: Industrial

## COUNTRY OF ORIGIN

Country Of Origin: MEXICO